






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
A1	-		C5	ECR-16-004045	24MAR2016	RR
			C6	ECR-16-010013	19JUL2016	RR
			C7	ECR-16-013486	26SEP2016	RR
			C8	ECR-17-005237	11APR2017	RR



- Notes
- 1 OBSOLETE
 - 2 PRELIMINARY - NOT RELEASED FOR PRODUCTION
 - 3 CONTACT ZONE SELECTIVE PRE SILVER PLATED MIN 1-1.5 µm

INSUL. RANGE Ø2.2-3.0 mm	WIRE RANGE >1-2.5 mm ²	2.5	 124 1826-1	vorverzinkt/PRETINNED	CuFe2	964203-1	C
		A	LP NO	FINISH	MATERIAL	PART NO.	REV
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN ATZMANN 06.01.94	 TE Connectivity			
			CHK BARTOSCH 18.01.94				
DIMENSIONS: mm			APVD Bleicher, M. 28.11.07	NAME STANDARD POWER TIMER KONTAKT (Gerade Tulpe)			
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1° ±0.2		PRODUCT SPEC 108-18025	- - -			
			APPLICATION SPEC 114-18037				
			MATERIAL -	FINISH -		WEIGHT 0.82 g	SIZE A 3
Customer Drawing			SCALE 5:1	SHEET 1	OF 9	REV C 8	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

(C) COPYRIGHT -

ALL RIGHTS RESERVED.

	LOC
--	-----

	DIST
--	------

REVISIONS

P

LTR

DESCRIPTION

DATE _____

	DW
--	----

APVD

--	--



SEE SHEET 1

--	--


--	--


ONLY FOR 3-927833-1 & 3-927833-2

OTHER DIMENSIONS SEE SHEET 1



2:1

INSUL. RANGE Ø2.7-3.7 mm	WIRE RANGE >1-2.5 mm ²	2.3±0.15	-	PRETINNED	CuSn4	3-927833-2	A
		2.3±0.15	-	PRETINNED	CuFe2	3-927833-1	A
		A	LP NO	FINISH	MATERIAL	PART NO.	REV
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ATZMANN	06.01.94	 TE Connectivity			
		CHK BARTOSCH	18.01.94				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Bleicher, M.	28.11.07	NAME STANDARD POWER TIMER KONTAKT (Gerade Tulpe)			
	0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±1° ±0.2	PRODUCT SPEC 108-18025		- SIZE A3 CAGE CODE 00779 DRAWING NO C-964203 RESTRICTED TO -			
		APPLICATION SPEC 114-18037					
MATERIAL -	FINISH -	WEIGHT 0.82 g					
Customer Drawing				SCALE 5:1	SHEET 2 OF 9		REV 8



ONLY FOR 3-927837-1, 3-927837-2,
3-927837-4 & 3-927837-5
OTHER DIMENSIONS SEE SHEET 1

X10CrNi188

6.85-0.15

0.25±0.03

0.4±0.05

0.4

max 0.5

3.3±0.1

max 0.08

B-B

3.8±0.3

4.1±0.3

A-A

4.8±0.3

4.9±0.3

2:1

INSUL. RANGE
Ø2.2-3.0
mm

WIRE RANGE
>1-2.5
mm²

2.3±0.15	-	PRESILVERED	CuFe2	3-927837-5	A
2.3±0.15	-	PRESILVERED	CuSn4	3-927837-4	A
2.3±0.15	-	PRETINNED	CuSn4	3-927837-2	A
2.3±0.15	-	PRETINNED	CuFe2	3-927837-1	A
A	LP NO	FINISH	MATERIAL	PART NO.	REV

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

±

±

±

±

±

±1°

±0.2

MATERIAL

-

FINISH

-

DWN
ATZMANN
CHK
BARTOSCH
APVD
Bleicher, M.
PRODUCT SPEC
108-18025
APPLICATION SPEC
114-18037
WEIGHT
0.82 g

06.01.94
18.01.94
28.11.07

NAME

STANDARD POWER TIMER KONTAKT
(Gerade Tulpe)
-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-964203

-


Customer Drawing


SCALE
5:1

SHEET
3 OF 9





REV
C8

1470-19 (3/11)




INSUL. RANGE Ø3.3-4.5 mm	WIRE RANGE >2.5-4.0 >mm ²	2.3±0.15	-	PRETINNED	CuSn4	3-927824-2	A		
		2.3±0.15	-	PRETINNED	CuFe2	3-927824-1	A		
		A	LP NO	FINISH	MATERIAL	PART NO.	REV		
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ATZMANN 06.01.94	TE TE Connectivity STANDARD POWER TIMER KONTAKT (Gerade Tulpe) -						
DIMENSIONS: mm		CHK BARTOSCH 18.01.94							
		APVD Bleicher, M. 28.11.07							
		PRODUCT SPEC 108-18025							
		APPLICATION SPEC 114-18037							
MATERIAL -		FINISH -	WEIGHT 0.82 g		SIZE A3		CAGE CODE 00779	DRAWING NO C-964203	RESTRICTED TO -
Customer Drawing				SCALE 5:1		SHEET 4 OF 9		REV C8	

ONLY FOR 3-927829-1 & 3-927829-5 ,
OTHER DIMENSIONS SEE SHEET 1



INSUL. RANGE Ø2.7-3.7 mm	WIRE RANGE >2.5-4.0 mm ²	2.3±0.15	-	PRESILVERED	3	CuFe2	3-927829-5	A
		2.3±0.15	-	PRETINNED		CuFe2	3-927829-1	A
		A	LP NO	FINISH		MATERIAL	PART NO.	REV

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ATZMANN	06.01.94	TE TE Connectivity				
		CHK BARTOSCH	18.01.94					
		APVD Bleicher, M.	28.11.07					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		STANDARD POWER TIMER KONTAKT (Gerade Tulpe)			
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1° ±0.2		PRODUCT SPEC		-			
		APPLICATION SPEC						
MATERIAL	FINISH		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-	-		0.82 g		A3	00779	C-964203	-
Customer Drawing					SCALE	SHEET		REV
					5:1	5 OF 9		C8

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

P

LTR

DESCRIPTION

DATE _____

	DWN
--	-----



APVD

SEE SHEET 1

—


ONLY FOR 3-964328-1

OTHER DIMENSIONS SEE SHEET 1



INSUL. RANGE Ø3.3-4.5 mm	WIRE RANGE >2.5-4.0 mm ²
--------------------------------	---

-	PRETINNED	CuFe2	3-964328-1	A
LP NO	FINISH	MATERIAL	PART NO.	REV
DWN ATZMANN	06.01.94	 TE Connectivity		
CHK BARTOSCH	18.01.94			
APVD Bleicher.M.	28.11.07	NAME		
PRODUCT SPEC 108-18025	STANDARD POWER TIMER KONTAKT (Gerade Tulpe) -			
APPLICATION SPEC 114-18037	SIZE	CAGE CODE	DRAWING NO	RESTRICTED T
WEIGHT <u>0.82 g</u>	A3	00779	©-964203	-
Customer Drawing			SCALE 5.1	SHEET 8 OF 9
			REV	8

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	 0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm 1^\circ$ ± 0.2
MATERIAL	FINISH
-	-

