

HONEYWELL PART NUMBER
1SX18-T
PRODUCT CODE VDA1850

REV	DOCUMENT	CHANGED BY	CHECK
6	0038446	KVB 20MAY08	BLR



B

A

A

B

A




NOTE -

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
- 4 - SWITCH HAS A GREATER OVERTRAVEL THAN STANDARD CONSTRUCTION. ADDITIONAL OVERTRAVEL WILL TEND TO REDUCE MECHANICAL LIFE

RELEASE NO. SR-12755

REPLACES -

CHARACTERISTICS	ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 			DRAWN	SPK	30NOV07	Honeywell			
OPERATING FORCE – – – – 5 OZ MAX	CONTACT ARRANGEMENT SPDT						CHECK	RJ	30NOV07				
RELEASE FORCE – – – – – 1 OZ MIN	28 VOLTS DC RATING			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC						
DIFFERENTIAL TRAVEL – – – .005 MAX		SEA LEVEL	50,000 FT										
OVERTRAVEL – – – – – .006 MIN	INDUCTIVE	4 AMP	2.5 AMP										
	RESISTIVE	7 AMP	7 AMP										
	MAXIMUM INRUSH 24 AMP												
	APPROVALS	KEMA, CE	7A 250V ~ T125 5E4 				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME	REV
		UL, CSA	7A 250 VAC   BRAND L7							B	I	1SX18-T	6
							RASTER			SCALE	-	WEIGHT: .003 LB MAX	SHEET 1 OF 1