





CIRCUIT: 2P: SPST
CONTACT CONFIGURATION
ON-OFF

SWITCH FUNCTION		
POS. 1	POS. 3	
ON	OFF	
1-2	OPEN	




2.20 +0.1/-0.0

RECOMMEND PANEL MOUNTING



RED ACTUATOR



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0 ± 0.4
 0.00 ± 0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 16A, 125VAC, 10A, 250VAC UL&CUL APPROVED
10A 125VAC, 6A 250V AC VDE APPROVED
5. CONTACT RESISTANCE: 50m ohm max.
6. INSULATION RESISTANCE: DC 500V 100M ohm min.
7. DIELECTRIC STRENGTHS: AC 1500V 1 minute
8. OPERATING TEMP.: 0°C to 85°C
9. ▲ DENOTES CRITICAL PARAMETER.
10. 2002/95/EC (ROHS) COMPLIANT

C	16972	ADDED ROHS NOTE, FIXED QAD	2/6/07	TN
B	15277	CONTACT FROM SPDT TO SPST	9/14/05	PH
A	15135	RELEASED FOR PRODUCTION	8/8/05	RC
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

E-SWITCH

TITLE
RR3112ABL KREDNFFD

SCALE	DATE	DR	DWG	REV
2:1	2/6/07	TN	F130425	C