





- 1 CONTACTS DESIGNED FOR 26 & 28 AWG STRANDED OR 26, 28 & 30 AWG SOLID WIRE.
- 2 AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.
- 3 STANDOFFS: POSN 8 (2) STANDOFFS AS SHOWN. POSN 14-20 (3) STANDOFFS, (1) CENTERED BETWEEN (2) SHOWN
- 4 PLATED WITH .000100 - .000200 BRIGHT TIN LEAD OVER .000050 NICKEL.
- 5 PLATED WITH .000030 GOLD OVER .000050 NICKEL.
- 6 GOLD FLASH OVER .000050 NICKEL.
- 7 HEIGHT AFTER TERMINATION IS .253 REF.
- 8 INDICATES NO 1 POSITION.
- 9 PLATED WITH .000005 MIN GOLD IN IDC AREA OVER .000050 MIN NICKEL.
- 10 MOLDED PARTS: 94V-0 RATED THERMOPLASTIC, COLOR BLACK. CONTACTS: PHOS BRONZE.



	9	5	6	.900	9	1.088	.900	.950	19	20	1- 746611 - 0
	9	5	6	.800	8	.988	.800	.850	17	18	↑ -9
	9	5	6	.600	6	.788	.600	.650	13	14	-8
	9	5	6	.300	3	.488	.300	.350	7	8	-7
	9	5	6	.700	7	.888	.700	.750	15	16	-6
OBSOLETE	4	5	6	.900	9	1.088	.900	.950	19	20	-5
OBSOLETE	4	5	6	.800	8	.988	.800	.850	17	18	-4
OBSOLETE	4	5	6	.700	7	.888	.700	.750	15	16	-3
OBSOLETE	4	5	6	.600	6	.788	.600	.650	13	14	↓ -2
OBSOLETE	4	5	6	.300	3	.488	.300	.350	7	8	746611 - 1
	CONTACT FINISH			F	E	D	C	B	A	NO OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN L. VARELA - DOCKS 11-29-04	 TE Connectivity				
DIMENSIONS: INCHES			CHK C. RÖHDE 11-29-04	NAME				
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD M. WALMSLEY 11-29-04	KIT, AMP-LATCH DIP PLUG, PREASSEMBLED .100 X .300 CENTERS, 30 GOLD DUPLEX CONTACTS				
0 PLC ± -			PRODUCT SPEC					
1 PLC ± -			108-40013					
2 PLC ± .005			APPLICATION SPEC					
3 PLC ± -			114-40005					
4 PLC ± -			WEIGHT					
ANGLES ± -			A1 00779					
MATERIAL			CUSTOMER DRAWING					
FINISH			SCALE 10:1					
CONTACTS: SEE TABLE			SHEET 1 OF 1					
			REV M					