



MATERIAL

stem- polypropylene white
nut- polypropylene white
float- polypropylene white
lock washer- polypropylene white
O-ring- nitril caoutchouc black

Schaft- Polypropylen weiss
Mutter- Polypropylen weiss
Schwimmer- Polypropylen weiss
Sicherungsring- Polypropylen weiss
O-Ring nitril Kautschuk schwarz

CABLE / Kabel

single wires LIYY/T 0.14 mm²
ends 5±1 mm stripped and tinned
Einzellitzen LIYY/T 0.14 mm²
Enden 5±1 mm abisoliert/verzinnt

MARKING / Aufdruck

Production code EN60062/
Factory code
Produktionscode
EN60062/Fertigungsstätte

Float specific density - approx. 0.7 g/cm³
Spezifisches Schwimmergewicht ca. 0.7 g/cm³

Special Product Data	Conditions	Min	Typ	Max	Unit
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
operating voltage	DC or Peak AC			175	VDC
operating ampere	DC or Peak AC			1	A
Switching current	DC or Peak AC			0,5	A
Sensor-resistance	measured with 40% overdrive			300	mOhm
Housing material				PP	
Case color				white	
Sealing compound				Polyurethan	

Environmental data	Conditions	Min	Typ	Max	Unit
Operating temperature	Cable not moved	-30		80	°C
Operating temperature	cable moved	-5		80	°C
Storage temperature		-30		80	°C
safety class	DIN EN 60529			IP68 until the thread	

Cable specification	Conditions	Min	Typ	Max	Unit
Cable typ				single wires	
Cable material				PVC	
Cross section				0,14 qmm	

General data	Conditions	Min	Typ	Max	Unit
Mounting advice				over 5m cable, a series resistor is recommended.	
Tightening torque				0,5	Nm