

Heat Shrinkable Tubing and Caps



✓ Active

Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

? Heat Shrinkable Tubing
? Product Name = VPB
? Product Source = U.K., U.S.
? Flexible
? Medium Wall Style

[View all Features](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

? None Available

? None Available

[THERMOFIT VITON POLYMER BLEND TUBING Fluoroelastomer...
\(PDF, English\)](#)

? None Available

? None Available

? None Available

List all Documents

? Product Line Information

? Tooling

? Product Type = Heat Shrinkable Tubing
 ? Material = Polymer Blend fluoroelastomer
 ? Color = Black
 ? CSA Certified = No

? Product Source = U.K., U.S.
 ? Expanded ID, Min. (mm [in]) = 9.53 [0.375]
 ? Recovered ID, Max. (mm [in]) = 4.80 [0.189]
 ? Product Use = Cables, Harnesses

- ? Product Name = VPB
- ? Pliancy = Flexible
- ? Wall Style = Medium
- ? Wall Type = Single
- ? Shrink Ratio = 2:1
- ? Fluid Resistance = Splash Protection
- ? Fluid Type = Aviation Fuel, Chemicals/Solvents, De-Icing Fluid, Diesel Fuel, Lubricating Oil, Unleaded Gasoline
- ? Resistant To = Abrasion, Fluids, Wrinkling
- ? Flammability Rating = Flame -Retardant
- ? UL Rating = None
- ? Wall Thickness - Full Recovery (Nominal) (mm [in]) = 0.88 [0.0346]

? Approved Standards = SC -X-15111

? Material Systems Code = 30

- ? Government/Industry Qualification = No
- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Full Recovery Temperature (°C) = 175
 ? Shrink Temperature, Min. (°C) = 100
 ? Operating Temperature (°C) = -55 – +150
 ? High Temperature Compatible = Yes

? Application = Cable Jacketing, Wire Bundling
? Emission Free = No

? Packaging Method = Spool

? Brand = Raychem