

RED INDICATES ORIGINAL


DASH NO.	MODEL NO.	LULOR	CABLE	
			TYPE	IMPD OHMS
-1	LPTW-78	BLUE	TWINAX	78
-2	LPTW-124		TWINAX	124
-3	LPTR-50	YFILDW	TRIAx	50
-4	LPTR-75		TRIAx	75
-5	LPTW-98	BLUE	TWINAX	98
-6	LPTW-0	BLUE	W/O	-




DATA CONTAINED IN THIS DOCUMENT IS
PROPRIETARY TO TROMPETER ELECTRONICS, INC.,
AND SHALL NOT BE DISCLOSED, COPIED OR USED
FOR PROCUREMENT OR MANUFACTURE WITHOUT
EXPRESS WRITTEN PERMISSION

REVISIONS				3-0012		SH :
REV	EO	DESCRIPTION		OWN	APPROVED	DATE
M	12402	ADDED ITEM 10; DELETED 2 ON ITEM 1; SEE ECO		DBN	<i>LM</i>	7/14/88

INCH	MM
.005	0.13
.010	0.25
.030	0.76
.125	3.18
.374	9.50
.540	13.72
.590	14.99
.625	15.88
1.200	30.48
2.250	57.15
2.825	71.76



.374 DIA TYP
±.005



- △ ASSEMBLED WITHOUT WIRE
TO BE USED AS A PLUG
- △ ALL CABLE ASSEMBLIES FOR -5 SHALL BE
EQUAL IN LENGTH TO WITHIN 0.125 INCHES
3. CONCENTRIC TWINAX/TRIAx STD
SPACING LOOPING PLUG
 2. FINISH: BARRELS; TFS-1A (NICKEL)
CASE: SEE TABLE
 1. ALL DIM ARE IN INCHES

NEXT ASSY

QTY	DESCRIPTION		PART NUMBER	ITEM
1	UNLESS SPECIFIED		 LPTW / LPTR	
	.XX ± .XXX ±.030 .XXXX ± ANGLES ±			
OWN	DBN	3/21/96	MATERIAL CODE IDENT	DRAWING NO
CHK	WMI	3-24-98	14949	3-0012
ENR				RCV
APPR	Eg	3/25/98	SCALE: 1/1	DATE 7/14/88
			SHEET 1 OF 2	