





PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



Notes:

- 1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6±0.15 mm.

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P91C4PL00LF	D09P91C6PL00LF	D09P91C8PL00LF
15	39.14	33.32	25.18	25.12	19.18	D15P91C4PL00LF	D15P91C6PL00LF	D15P91C8PL00LF
25	53.03	47.04	39.12	38.84	33.12	D25P91C4PL00LF	D25P91C6PL00LF	D25P91C8PL00LF
37	69.32	63.50	55.68	55.30	49.68	D37P91C4PL00LF	D37P91C6PL00LF	D37P91C8PL00LF
gold flash							0.76μ gold	1.25μ gold

mat'l. code				surface	tolerance	projection	product family	
-				ISO 1302	ISO 406 ISO 1101	MM	D-SUB	
ltr	ecn no	dr	date	tolerances unless otherwise specified				title
L	ELX-I-21256	AB	2015/07/14	angles	linear	scale 2:1	MALE CONNECTOR DELTA-D STRAIGHT - PRESS FIT	
				0±2°	.0±0.1 .00±0.1 .000±0.1		dwg no	sheet 1 of 1 size
				dr	JARRY	1992/09/14	C01-8646-0110	
				engr	ALIAS BABU	2015/07/14	A3	
				chr	MITHUN PAUL	2015/07/14	type Product Customer Drawing	
				app	BIJU K PAUL	2015/07/14		
sheet index	revision	L						
	sheet	1						