

Technical drawing illustrating the dimensions and components of a Nylon Plastic Cinch Ring. The drawing shows two views: a side view (top) and a cross-sectional view (bottom).

Top View (Side View):

- C REF.:** Dimension indicating the reference width of the ring.
- B:** Dimension indicating the thickness of the ring.
- E:** Dimension indicating the height of the ring.
- F REF.:** Dimension indicating the reference length of the ring.
- NYLON PLASTIC CINCH RING:** Label identifying the component.

Bottom View (Cross-sectional View):

- A:** Dimension indicating the thickness of the material being cinched.
- D:** Dimension indicating the thickness of the ring.

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/100 PARTS (g)
	MIN. in (mm)	MAX. in (mm)									
UCT3S	.63 (16.0)	3.0 (76.2)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	12.0 (305)	50 (222)	STANDARD	.59 (267)
UCT5S	.63 (16.0)	5.0 (127)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	18.0 (457)	50 (222)	STANDARD	.81 (366)

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

SS_27366_00.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

TAK-TY HOOK & LOOP CABLE TIES
ULTRA-CINCH HOOK & LOOP TIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .25 (.XXX) ± .030
(.XX) ± .125 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JABO

MAT'L:

SCALE NONE

DATE	6/19/02
------	---------

WOVEN NYLON
HOOK/LOOP
COLOR: BLACK

DRAWING NO.

SS-27366

DWG
A
SIZE

7	4/12/06	FAB		ADDED PART WEIGHTS	27366	7			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	