


# 2.54mm Connector Directly Mounted on Board

## HIF2E Series



### ■Features

#### 1. Directly Mounted on Board

This connector can be directly mounted on the board using the 1.27mm pitch flat cable.

#### 2. Variation in Number of Contacts

10, 14, 16, 20, 26, 30, 34, 40, 50, and 60 contacts, are available

#### 3. Applicable Cable

The applicable cable is UL2651 AWG#28 flat cable (7 cores/0.127mm, jacket dia. :0.8 to 1.0mm).

### ■Applications

Computers, terminal equipment, PPC, various kinds of electronic equipment, office automation machines, etc.

### ■Product Specifications

|        |                          |                                                     |                                                   |
|--------|--------------------------|-----------------------------------------------------|---------------------------------------------------|
| Rating | Current rating : 1A      | Operating Temperature Range : -55 to +85°C (Note 1) | Storage Temperature Range : -10 to +60°C (Note 2) |
|        | Voltage rating : 200V AC | Operating Moisture Range : 40 to 80%                | Storage Humidity Range : 40 to 70% (Note 2)       |

| Item                            | Specification                                       | Condition                                                                                                   |
|---------------------------------|-----------------------------------------------------|-------------------------------------------------------------------------------------------------------------|
| 1. Insulation Resistance        | 1000M ohms min                                      | 500V DC                                                                                                     |
| 2. Withstanding voltage         | No flashover or insulation breakdown.               | 650V AC/1 minute                                                                                            |
| 3. Contact Resistance           | 15m ohms max                                        | 0.1A                                                                                                        |
| 4. Vibration                    | No electrical discontinuity of 1μs or more          | Frequency: 10 to 55 Hz, single amplitude of 0.75 mm, 2 hours in each of the 3 directions.                   |
| 5. Humidity (Steady state)      | Insulation resistance: 1000M ohms min.              | 96 hours at temperature of 40°C and humidity of 90% to 95%                                                  |
| 6. Temperature Cycle            | No damage, cracks, or parts looseness.              | (-65°C: 30 minutes → 15 to 35°C: 5 minutes max.<br>125°C: 30 minutes → 15 to 35°C: 5 minutes max.) 5 cycles |
| 7. Resistance to Soldering heat | No deformation of components affecting performance. | Solder bath: 260°C for 10 seconds                                                                           |
|                                 |                                                     | Manual soldering: 360°C for 5 seconds                                                                       |

Note 1: Includes temperature rise caused by current flow.

Note 2: The term "storage" refers to products stored for long period of time prior to mounting and use. Operating Temperature Range and Humidity range covers non conducting condition of installed connectors in storage, shipment or during transportation.

Note 3: Information contained in this catalog represents general requirements for this Series. Contact us for the drawings and specifications for a specific part number shown.

### ■Material

| Part      | Material     | Finish                              |                  | Remarks |
|-----------|--------------|-------------------------------------|------------------|---------|
| Insulator | PBT          | Black                               | HIF2E-*D-2.54R B | UL94V-0 |
|           |              | Gray                                | HIF2E-*D-2.54R A |         |
| Contact   | Copper alloy | Gold plated over nickel underplated |                  | ——      |

### ■Ordering Information


**HIF2E - \* D - 2.54 RB**

①                      ②                      ③                      ④                      ⑤

|                                                                   |                                                                                                                           |
|-------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| ① Series Name : HIF2E                                             | ⑤ Connection method and contact plating type<br>RB : Universal type circuit plated<br>RA : Hirose original circuit plated |
| ② Number of Contacts : 10, 14, 16, 20, 26, 30, 34, 40, 50, and 60 |                                                                                                                           |
| ③ Contact alignment : D : Double                                  |                                                                                                                           |
| ④ Contact Pitch : 2.54mm                                          |                                                                                                                           |

HIF2E Series 2.54mm Connector Directly Mounted on Board


■Combination Pattern




Unit: mm

|   | 10 contacts | 14 contacts | 16 contacts | 20 contacts | 26 contacts | 30 contacts | 34 contacts | 40 contacts | 50 contacts | 60 contacts |
|---|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|
| A | 17.17       | 22.25       | 24.79       | 29.87       | 37.49       | 42.57       | 47.65       | 55.27       | 67.97       | 80.67       |
| B | 10.16       | 15.24       | 17.78       | 22.86       | 30.48       | 35.56       | 40.64       | 48.26       | 60.96       | 73.66       |

◆PCB mounting pattern




## ■Universal Circuit Type (Mold color: black)



Unit:mm

| Part Number      | CL No.     | Number of Contacts | A     | B     | RoHS |
|------------------|------------|--------------------|-------|-------|------|
| HIF2E-10D-2.54RB | 561-0601-1 | 10                 | 17.17 | 10.16 | YES  |
| HIF2E-14D-2.54RB | 561-0602-4 | 14                 | 22.25 | 15.24 |      |
| HIF2E-16D-2.54RB | 561-0603-7 | 16                 | 24.79 | 17.78 |      |
| HIF2E-20D-2.54RB | 561-0604-0 | 20                 | 29.87 | 22.86 |      |
| HIF2E-26D-2.54RB | 561-0605-2 | 26                 | 37.49 | 30.48 |      |
| HIF2E-30D-2.54RB | 561-0606-5 | 30                 | 42.57 | 35.56 |      |
| HIF2E-34D-2.54RB | 561-0607-8 | 34                 | 47.65 | 40.64 |      |
| HIF2E-40D-2.54RB | 561-0608-0 | 40                 | 55.27 | 48.26 |      |
| HIF2E-50D-2.54RB | 561-0609-3 | 50                 | 67.97 | 60.96 |      |
| HIF2E-60D-2.54RB | 561-0610-2 | 60                 | 80.67 | 73.66 |      |

## ■Hirose Original Circuit Type (Mold color: gray)



Unit:mm


| Part Number      | CL No.     | Number of Contacts | A     | B     | RoHS |
|------------------|------------|--------------------|-------|-------|------|
| HIF2E-10D-2.54RA | 561-0501-7 | 10                 | 17.17 | 10.16 | YES  |
| HIF2E-14D-2.54RA | 561-0502-0 | 14                 | 22.25 | 15.24 |      |
| HIF2E-16D-2.54RA | 561-0503-2 | 16                 | 24.79 | 17.78 |      |
| HIF2E-20D-2.54RA | 561-0504-5 | 20                 | 29.87 | 22.86 |      |
| HIF2E-26D-2.54RA | 561-0505-8 | 26                 | 37.49 | 30.48 |      |
| HIF2E-30D-2.54RA | 561-0506-0 | 30                 | 42.57 | 35.56 |      |
| HIF2E-34D-2.54RA | 561-0507-3 | 34                 | 47.65 | 40.64 |      |
| HIF2E-40D-2.54RA | 561-0508-6 | 40                 | 55.27 | 48.26 |      |
| HIF2E-50D-2.54RA | 561-0509-9 | 50                 | 67.97 | 60.96 |      |
| HIF2E-60D-2.54RA | 561-0510-8 | 60                 | 80.67 | 73.66 |      |

## HIF2E Series 2.54mm Connector Directly Mounted on Board


### ◆ Connection Circuit Diagram

#### HIF2E-\*D-2.54RB

##### ● Type A-A




##### ● Type A-B




#### HIF2E-\*D-2.54RA

##### ● Type A-A



##### ● Type A-B



Note: In the above circuit connection diagram, the mark and character marking directions are optional.