



THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RESONANT FREQUENCY	2,000±500	Hz
RESONANT IMPEDANCE (MAX)	300	Ohm
MAX INPUT VOLTAGE	20	V _{p-p}
CAPACITANCE @ 120Hz	90,000±30%	pF
PLATE MATERIAL	ALLOY	—
OPERATING TEMPERATURE	-20 ~ +70	°C
STORAGE TEMPERATURE	-30 ~ +80	°C



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
AB2020A.DWG

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	11/6/01	
A	REVISED TO NEW TEMPLATE	8/29/03	R. W.
B	REVISED SPECIFICATIONS	1/9/04	R. W.
C	REVISED SPECIFICATIONS	2/11/05	R. W.
D	REVISED RESONANT FREQUENCY	2/16/05	R. W.
E	REVISED DIMENSION SIZE AND STYLE	12/20/05	B. R.
F	REVISED CERAMIC DIMENSION	1/30/08	B. R.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN <i>RABL</i>	11/01
APPROVED <i>S. J.</i>	11/01

DO NOT SCALE DRAWING



projects®
unlimited

Dayton, Ohio

PIEZO CERAMIC BENDER

SIZE A DRAWING NO.
AB2020A

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AB2020A](#)