


Dimensions: mm (In)

**Electrical Specifications:**

- Rating: 3A/125V, 1.5A/250VAC
- Contact resistance: 50m Ω max
- Insulation resistance: 500VDC 100m Ω min
- Dielectric strength: 1000VAC 1 minute

Mechanical Specifications:

- Circuit: 2P SPST on-off

Toggle Switch
103-0132

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-0132](#)