



Micro Commercial Components



Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

MMBT2907AT

PNP General Purpose Amplifier

Features

- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant. See ordering information)
- Capable of 150mWatts of Power Dissipation
- Operating and Storage Junction Temperatures -55°C to 150°C
- Collector Current: -0.6A
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Marking:2F
- Halogen free available upon request by adding suffix "-HF"

Electrical Characteristics @ 25°C Unless Otherwise Specified

Symbol	Parameter	Min	Max	Units
OFF CHARACTERISTICS				
$V_{(BR)CEO}$	Collector-Emmitter Breakdown Voltage* ($I_C = -10\text{mA}$, $I_B = 0$)	-60		Vdc
$V_{(BR)CBO}$	Collector-Base Breakdown Voltage ($I_C = -10\mu\text{A}$, $I_E = 0$)	-60		Vdc
$V_{(BR)EBO}$	Emitter-Base Breakdown Voltage ($I_E = -10\mu\text{A}$, $I_C = 0$)	-5.0		Vdc
I_{CBO}	Collector Cut-off Current ($V_{CB} = -50\text{Vdc}$, $I_E = 0$)		-10	nAdc
I_{EBO}	Emitter Cut-off Current ($V_{EB} = -4\text{Vdc}$, $I_C = 0$)		-10	nAdc

ON CHARACTERISTICS

h_{FE}	DC Current Gain* ($I_C = -0.1\text{mA}$, $V_{CE} = -10\text{Vdc}$) ($I_C = -1.0\text{mA}$, $V_{CE} = -10\text{Vdc}$) ($I_C = -10\text{mA}$, $V_{CE} = -10\text{Vdc}$) ($I_C = -150\text{mA}$, $V_{CE} = -10\text{Vdc}$) ($I_C = -500\text{mA}$, $V_{CE} = -10\text{Vdc}$)	75 100 100 100 50	300	
$V_{CE(sat)}$	Collector-Emmitter Saturation Voltage ($I_C = -150\text{mA}$, $I_B = -15\text{mA}$) ($I_C = -500\text{mA}$, $I_B = -50\text{mA}$)		-0.4 -1.6	Vdc
$V_{BE(sat)}$	Base-Emmitter Saturation Voltage ($I_C = -150\text{mA}$, $I_B = -15\text{mA}$) ($I_C = -500\text{mA}$, $I_B = -50\text{mA}$)		-1.3 -2.6	Vdc


SMALL-SIGNAL CHARACTERISTICS

f_T	Current Gain-Bandwidth Product ($I_C = -2\text{mA}$, $V_{CE} = -12\text{Vdc}$, $f = 30\text{MHz}$)	140(Typ.)		MHz
C_{cbo}	Output Capacitance ($V_{CB} = -12\text{Vdc}$, $I_E = 0$, $f = 100\text{kHz}$)		5.0	pF

SWITCHING CHARACTERISTICS

T_{on}	Turn-on Time	$(V_{CC} = -30\text{Vdc}, I_C = -150\text{mA}, I_{B1} = -15\text{mA})$	45	ns
t_d	Delay Time		10	ns
t_r	Rise Time		40	ns
t_{off}	Turn-off Time	$(V_{CC} = -6\text{Vdc}, I_C = -150\text{mA}, I_{B1} = I_{B2} = -15\text{mA})$	100	ns
t_s	Storage Time		80	ns
t_f	Fall Time		30	ns

SOT-523



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.059	.067	1.50	1.70	
B	.030	.033	0.75	0.85	
C	.057	.069	1.45	1.75	
D	.020 Nominal		0.50 Nominal		
E	.035	.043	0.90	1.10	
G	.000	.004	.000	.100	
H	.028	.031	.70	0.80	
J	.004	.008	.100	.200	
K	.010	.014	.25	.35	




Fig.1 Grounded emitter output characteristics




Fig.2 Base-emitter saturation voltage vs. collector current




Fig.3 DC current gain vs. collector current (I)

Ordering Information :

Device	Packing
Part Number-TP	Tape&Reel; 3Kpcs/Reel

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.