


samtec

HLS-0308-G-2



CARRIER STRIPS HLS & HLT SERIES

Mates with:

TS-1, HTS, BBS, BBL, BHS, BBD, BDL, LBS, HLT, TSB

Lead sockets "float" and "self-center" when this low profile carrier is soldered. Ideal for most VP or IR processes.

SPECIFICATIONS


For complete specifications see www.samtec.com?HLS

Same as SL-1 except:
Insulator Material:
 Black High Temperature Thermoplastic
Temperature Range:
 -55°C to +140°C
Heat Deflection Temp:
 215°C @ 264 psi

Note:

This Series is non-standard, non-returnable.

HLS	NO. ROWS	NO. PINS PER ROW	PLATING OPTION	LEAD STYLE	OPTION
Total Pins = No. Rows x No. Pins Per Row		-01 thru -20 (requires both digits)	-G = 30μ"(0,76μm) Gold Contact 10μ"(0,25μm) Gold Shell		-L = Locking Socket
			-T = 30μ"(0,76μm) Gold Contact Tin Shell		
			-S = 10μ"(0,25μm) Gold Contact Tin Shell (Styles 2 & 22 only)		
			-TT = Tin Contact and Shell (Styles 2, 10, 11, 12, 18, 22, 30, 31 & 32 only)		




Total Pins = No. Rows x No. Pins Per Row

-01 thru -20
(requires both digits)

Low Insertion Force (LIF) Available


-2 or -18 = Standard Socket For LIF specify -22 or -38



*Locking Lead Available. See Option.


Lead DIA Accepted = .015" to .022"
 Insertion Depth = .095" to .150"
 Style 2 Component Part No. = SC-1P1
 Style 18 Component Part No. = SC-6P1
 Style 38 Component Part No. = EZ-6P1

-3 = Body Only For LIF specify -23




Lead DIA Accepted = .015" to .022"
 Insertion Depth = .125" to .175"
 Style 3 Component Part No. = SC-1S1
 Style 23 Component Part No. = EZ-1S1

-10 = Low Profile Hollow Leg For LIF specify -30




Lead DIA Accepted = .015" to .022"
 Insertion Depth = .105" to .170"
 Style 10 Component Part No. = SC-3P1
 Style 30 Component Part No. = EZ-3P1

-11 = Low Profile Standard For LIF specify -31




Lead DIA Accepted = .016" to .021"
 Insertion Depth = .080" to .115"
 Style 11 Component Part No. = SC-4P1
 Style 31 Component Part No. = EZ-4P1

-12 = Micro Socket For LIF specify -32



Lead DIA Accepted = .016" to .020"
 Insertion Depth = .080" to .150"
 Style 12 Component Part No. = SC-5P1
 Style 32 Component Part No. = EZ-5P1

-14 or -15 = Short Tail



Lead DIA Accepted = .015" to .022"
 Style 14 Insertion Depth = .125" to .150"
 Style 14 Component Part No. = SC-1M1
 Style 15 Insertion Depth = .080" to .110"
 Style 15 Component Part No. = SC-1M2

Mates with:
 SS-1, SD-1, HSS, SL, SDL, ESS, ESD, HLS

SPECIFICATIONS





For complete specifications see www.samtec.com?HLT

Same as HLS except:
Terminal Material:
 Brass
Plating:
 Au or Sn over 50μ"(1,27μm) Ni
Current Rating:
 1A

Note:

This Series is non-standard, non-returnable.

HLT	NO. ROWS	NO. PINS PER ROW	PLATING OPTION	LEAD STYLE
Total Pins = No. Rows x No. Pins Per Row		-01 thru -20 (requires both digits)	-G = 20 μ"(0,51 μm) Gold	-R
		01 thru 20 (requires both digits)	-T = Tin	-H
				-T = Short Tail



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047
 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299
 SAMTEC SCANDINAVIA • Tel: +46-84477280 • Fax: +46-847420413
 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502
 SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842
 SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340
 SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681
 SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520
 SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61
 SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-61103766
 SAMTEC SOUTH AFRICA • Tel: 27 11 4528112 • Fax: 27 86 6714432
 SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113
 SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315
 SAMTEC INDIA • Tel: 91 80 306 21 612 • Fax: 91 80 4152 8187
 SAMTEC TAIWAN • Tel: 886 02 2698-3367 • Fax: 886 02 8698-2159
 SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745