


VENAUFTRAGSPEZ. 114-10756		SIZE	CAGE CODE	DRAWING NO ZEICHNUNGS-NR.	RESTRICTED TO MIL FUEL	
WEIGHT GEWICHT	24.1 g	A1	00779	C=1564514	-	
CUSTOMER DRAWING		KUNDENZEICHNUNG		SCALE MASSSTAB	2:1	SHEET BLATT
				1	OF VON	1
					REV	13

POLARIZATION- Polarisierungen



TE ORDER-NO. TE Bestell-Nr.	REV.	NO. OF POS. Polzahl	CODE Kodierung	COLOR OF CAVITY BLOCK Farbe des Kammerblocks	QUANTITY Stueck	ITEM NO ASSY
4-1564514-1	J	10	D	BLUE blau	1	4
3-1564514-1	J	10	C	GREEN gruen	1	3
2-1564514-1	J	10	B	GREY grau	1	2
1-1564514-1	J	10	A	BLACK schwarz	1	1

MATERIAL	FINISH/OBERFLÄCHE/FARBE
SEE TABLE	SEE TABLE
siehe Tabelle	siehe Tabelle

APPLICATION SPEC	
VERARBEITUNGSSPEZ.	
114-18756	

NAME 10POS. AMP MCP 2.8/1.5K, REC HSG, ASSY
10pos. AMP MCP 2.8/1.5k, Buchsengehaeuse
HDSCS - GROUP D

SIZE A 4	CAGE CODE	DRAWING NO ZEICHNUNGS-NR.	RESTRICTED TO NUR FÜR
-------------	-----------	------------------------------	--------------------------

A	00779	C=1564514			-
KUNDENZEICHUNG		SCALE	2:1	SHEET	1 OF 1
					REV 13