




INCANDESCENT BULB

PARAMETERS		SYMBOL	MAX.	UNITS
LAMP VOLTAGE (DC)		V	6	V
POWER DISSIPATION		P _D	2	Watts
CURRENT		I	200	mA




PANEL THICKNESS	X dimension
0.75-1.25 [0.30-0.49]	19.2-0.1 [0.756]
1.25-2.0 [0.49-0.79]	19.4-0.1 [0.764]
2.0-3.0 [0.79-1.18]	19.8-0.1 [0.780]



(ILLUMINATED)
CIRCUIT: DPST
PANEL CUTOUT
NOT TO SCALE

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. RATING:
6A @250VAC;9A @125VAC (UL, CSA, VDE)
4(1)A @250VAC
4. LAMP VOLTAGE: 6VDC (INCANDESCENT BULB)
5. MATERIAL:
CONTACT SURFACE: Coin Silver, Silver Plate
TERMINAL: Copper Alloy w/ Silver Plate,
6. CONTACT RESISTANCE: 20miliohms TYP. INITIAL
7. INSULATION RESISTANCE: 1000Megohms
8. DIELECTRIC STRENGTH:
>1500V RMS min. @SEA LEVEL
>3000V RMS @SEA LEVEL
9. MECHANICAL LIFE: 50,000 CYCLES.
10. ELECTRICAL LIFE: 10,000 CYCLES.
11. ▲ DENOTES CRITICAL PARAMETER.



E-SWITCH®

TITLE			
A	13305	RELEASED FOR PRODUCTION	7/21/03
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
R1973BBLKBLIF6			
SCALE	2:1	DATE	7/21/03
DR	AR	DWG	M400073
REV	A		