



	10	9	8	7	6	5	4	3	2	1			
	MATERIAL NO. LOOSE PIECE	ENG. NO.	MATERIAL NO. TAPE MOUNTED	ENG. NO.	STUD SIZE	"S" ±.003/(0.08)	"W" MAX.	"C" MIN.	"L" MAX.	"ID" MIN.	STOCK THICKNESS	"H" ±.020/0.51	
F	190690027	AA-120-02	190690028	AA-120-02T	2	.094/(2.39)	.235/(6.00)	.157/(3.99)	.484/(12.29)	.062/(1.57)	.028/(0.71)	1.155/(29.34)	F
	190690029	AA-120-04	190690030	AA-120-04T	4	.119/(3.02)							
	190690031	AA-120-06	190690032	AA-120-06T	6	.146/(3.71)							
	190690033	AA-121-06	190690034	AA-121-06T	6	.146/(3.71)							
	190690035	AA-121-08	190690036	AA-121-08T	8	.173/(4.39)							
E	190690037	AA-121-10	190690038	AA-121-10T	10	.198/(5.03)	.322/(8.18)	.270/(6.86)	.641/(16.28)	.062/(1.57)	.028/(0.71)	1.155/(29.34)	E
	190690039	AA-121-209	190690475	AA-121-209T	209	.209/(5.18)							
	190690040	AA-122-10	190690041	AA-122-10T	10	.198/(5.03)							
	190690042	AA-122-14	190690044	AA-122-14T	14	.265/(6.71)							
	190690045	AA-122-56	190690046	AA-122-56T	56	.328/(8.33)							
D	190690047	AA-126-10	-----	-----	10	.198/(5.03)	.544/(13.82)	.552/(14.02)	1.034/(26.26)	.055/(1.40)	.031/(0.79)	1.342/(34.09)	D
	190690048	AA-126-14	190690128	AA-126-14T	14	.265/(6.71)							
	190690051	AA-126-56	-----	-----	56	.328/(8.33)							
	190690049	AA-126-38	190690050	AA-126-38T	38	.390/(9.91)							
	190690052	AA-132-04	190690053	AA-132-04T	4	.119/(3.02)							
	190690054	AA-132-06	190690055	AA-132-06T	6	.146/(3.71)	.264/(6.70)	.240/(6.10)	.582/(14.78)	.062/(1.57)	.028/(0.71)	1.155/(29.34)	
	190690056	AA-132-08	190690057	AA-132-08T	8	.146/(3.71)							
	190690061	AA-133-10	190690062	AA-133-10T	10	.198/(5.03)							
	190690024	AA-1111-02	190690191	AA-1111-02T	2	.094/(2.39)							
	190690025	AA-1111-04	190690026	AA-1111-04T	4	.119/(3.02)							



SALES DRAWING

NOTE(S):
1. MATERIAL: COPPER.
2. PLATING: ELECTRO-TIN.
3. ALL DIMENSIONS IN INCHES/(MM).

WIRE SIZE:
22-18 AWG
0.25-1.5 MM²

.265 DIM WAS .256 EC NO: ETC2006-0015 DRWN: JMYRICK 2005/07/22 CHKD: JPAWLICK 2005/07/22 APPR: JPAWLICK 2005/07/25	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><th></th><th>mm</th><th>INCH</th></tr><tr><td>4 PLACES</td><td>±---</td><td>±---</td></tr><tr><td>3 PLACES</td><td>±---</td><td>±---</td></tr><tr><td>2 PLACES</td><td>±---</td><td>±---</td></tr><tr><td>1 PLACE</td><td>±---</td><td>±---</td></tr><tr><td>ANGULAR</td><td>±---</td><td>°</td></tr></table>		mm	INCH	4 PLACES	±---	±---	3 PLACES	±---	±---	2 PLACES	±---	±---	1 PLACE	±---	±---	ANGULAR	±---	°	DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
	mm	INCH																							
4 PLACES	±---	±---																							
3 PLACES	±---	±---																							
2 PLACES	±---	±---																							
1 PLACE	±---	±---																							
ANGULAR	±---	°																							
DRAWN BY BDEROSS	DATE 2000/6/13	TITLE RING TONGUE TERMINAL KRIMPITE, 100 SERIES 22-18 AWG																							
CHECKED BY JHACKNEY	DATE 2000/6/13	MOLEX INCORPORATED																							
APPROVED BY BDEROSS	DATE 2000/6/13	DOCUMENT NO. SD-19069-004																							
C	REV	DESCRIPTION	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NO. 1 OF 1																				
			SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19069-0521](#)