

9207 Twinax - Twinaxial Cable

For more Information
please call

1-800-Belden1

**Description:**

20 AWG stranded (7x28) one tinned copper conductor, one bare copper conductor, polyethylene insulation, polyethylene inner jacket, Duofoil® (100% coverage) plus a tinned copper braid shield (86% coverage), PVC outer jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	7x28	TC - Tinned Copper	0.9398
			BC - Bare Copper	

Insulation

Insulation Material:

Insulation Material
PE - Polyethylene

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (mm)
PE - Polyethylene	5.9944

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	85

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Nominal Diameter: 8.382 mm

Pair

Pair Color Code Chart:

Number	Color
1	Natural & Natural

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +75°C
Bulk Cable Weight:	89.292 Kg/Km
Max. Recommended Pulling Tension:	498.198 N
Min. Bend Radius (Install)/Minor Axis:	88.900 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMG, CL2
CEC/C(UL) Specification:	CMG
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Customer Part Number Reference Specification:	IBM P/N 7362211

Flame Test

UL Flame Test:	UL1685 FT4 Loading
C(UL) Flame Test:	FT4

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes - when supported by a messenger wire

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	89207

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

100

Nom. Inductance:

Inductance (μH/m)

0.508555

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

47.5745

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

75.463

Nominal Velocity of Propagation:

VP (%)

66

Nominal Delay:

Delay (ns/m)

5.05274

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

31.1695

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

5.70894

Nom. Attenuation:

METRIC MEASUREMENT VERSION

9207 Twinax - Twinaxial Cable

Freq. (MHz)	Attenuation (dB/100m)
1	0.9843
10	3.9372
50	9.1868
100	13.4521
200	20.9984
400	33.4662

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Operating Voltage - Non-UL:

Voltage
600 V RMS

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9207 010U500	152 MT	14.969 KG	BLACK		100 OHM TWINAX
9207 010100	30 MT	3.221 KG	BLACK		100 OHM TWINAX
9207 0101000	305 MT	30.844 KG	BLACK	C	100 OHM TWINAX
9207 0101640	500 MT	50.585 KG	BLACK	C	100 OHM TWINAX
9207 0102000	610 MT	61.689 KG	BLACK	C	100 OHM TWINAX
9207 0103280	1,000 MT	99.682 KG	BLACK	C	100 OHM TWINAX
9207 010500	152 MT	15.649 KG	BLACK	C	100 OHM TWINAX
9207 0105000	1,524 MT	158.758 KG	BLACK	C	100 OHM TWINAX

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.