





MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
 per Tusonix standard
 test plans and Mil-Std-202
 Test Methods.



Cx (pF)	WVDC (125°)	CURRENT I _{dc}	IR (MIN.)	Min. No Load Insertion Loss (dB) at 25°C per Mil-Std-220			
				10 MHz	50 MHz	100 MHz	1-10 GHz
4000/8000	50	15 A	10GΩ	10	20	35	70

X-2015 Rev-0

REVISION RECORD			
0	Original Release C.O.		
1	REVISED LEAD DIMS. S.M. 01-03-96		
2	WAS SK 7265-000-S. S.M. 04-22-97		
3	970416-3 RADIUS REDRAWN TO SCALE ORIENTATION SYMBOL ADDED TOL'S .010 WAS .004 L.E. 02-14-03		
	20030213-6-02		

--TOLERANCES--
 Unless Otherwise Specified

DECIMAL ± $\frac{.010}{[0.25]}$

ANGLES ± $\frac{\quad}{\quad}$

TUSONIX
 TUCSON, ARIZONA

Title
FILTER PLATE

Drawn E.C. 10-16-95 Scale 2 X

Approved B.Mc. 10-16-95

A **7310-012**