



MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

General Description

The MAX44259/MAX44260/MAX44261/MAX44263 offer a unique combination of high speed, precision, low noise, and low-voltage operation making them ideally suited for a large number of signal processing functions such as filtering and amplification of signals in portable and industrial equipment.

The amplifiers feature an input offset of less than 50 μ V and a high-gain bandwidth product of 15MHz while maintaining a low 1.8V supply rail. The devices' rail-to-rail input/outputs and low noise guarantee maximum dynamic range in demanding applications such as 12- to 14-bit SAR ADC drivers. Unlike traditional rail-to-rail input structures, input crossover distortion is absent due to an optimized input stage with an ultra-quiet charge pump.

The MAX44260 includes a fast-power-on shutdown mode for further power savings. The MAX44261 offers a unique on-demand calibration pin where the user can invoke self-trimming of the input offset voltage. The MAX44263 is a dual amplifier.

The family of parts operates from a supply range of 1.8V to 5.5V over the -40°C to +125°C temperature range and can operate down to 1.7V over the 0°C to +70°C temperature range. The MAX44259 is offered in a 5-pin SOT23 package. The MAX44260/MAX44261 are available in small, 6-pin SC70 packages. The MAX44260 is also available in a 1mm x 1.5mm thin μ DFN (ultra-thin LGA) package. The MAX44263 is available in a small 8-pin SC70 package.

Visit www.maximintegrated.com/products/patents for product patent marking information.

Features


- ♦ Low 1.8V Supply Rail Over the -40°C to +125°C Range
- 1.7V Supply Rail Over the 0°C to +70°C Range
- ♦ 15MHz Unity-Gain Bandwidth
- ♦ Low 12.7nV/ $\sqrt{\text{Hz}}$ Input Voltage-Noise Density
- ♦ Low 1.2fA/ $\sqrt{\text{Hz}}$ Input Current-Noise Density
- ♦ Low 50 μ V (max) V_{OS} at +25°C
- ♦ On-Demand V_{OS} Self-Calibration (MAX44261)
- ♦ 500fA Low Input Bias Current
- ♦ 750 μ A Quiescent Current per Amplifier
- ♦ < 1 μ A Supply Current in Shutdown
- ♦ Small, 2mm x 2mm SC70 and 1mm x 1.5mm Thin μ DFN (MAX44260) and SOT23 (MAX44259) Packages
- ♦ Low 110dB Total Harmonic Distortion

Applications

Notebooks
3G/4G Handsets
Portable Media Players
Portable Medical Instruments
Battery-Operated Devices
Analog-to-Digital Converter Buffers
Transimpedance Amplifiers
General-Purpose Signal Processing

Ordering Information appears at end of data sheet.

Typical Application Circuit



For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim's website at www.maximintegrated.com.

MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

ABSOLUTE MAXIMUM RATINGS

IN+, IN-, OUT	(V_{SS} - 0.3V) to (V_{DD} + 0.3V)
V_{DD} to V_{SS}	-0.3V to +6V
\overline{SHDN} , \overline{CAL}	-0.3V to +6V
Output to Short-Circuit Ground Duration	10s
Continuous Input Current into Any Pin	± 20 mA
Continuous Power Dissipation ($T_A = +70^\circ\text{C}$)	
SC70 (derate 3.1mW/ $^\circ\text{C}$ above $+70^\circ\text{C}$)	245mW

SOT23 (derate 3.9mW/ $^\circ\text{C}$ above $+70^\circ\text{C}$)	312.6mW
6-Pin Thin μ DFN (Ultra-Thin LGA) (derate 2.1mW/ $^\circ\text{C}$ above $+70^\circ\text{C}$)	110.2mW
Operating Temperature Range	-40 $^\circ\text{C}$ to +125 $^\circ\text{C}$
Junction Temperature	+150 $^\circ\text{C}$
Lead Temperature (soldering, 10s)	+300 $^\circ\text{C}$
Soldering Temperature (reflow)	+260 $^\circ\text{C}$

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

PACKAGE THERMAL CHARACTERISTICS (Note 1)

SC70

Junction-to-Ambient Thermal Resistance (θ_{JA}) 326.5 $^\circ\text{C}/\text{W}$
Junction-to-Case Thermal Resistance (θ_{JC}) 115 $^\circ\text{C}/\text{W}$

SOT23

Junction-to-Ambient Thermal Resistance (θ_{JA}) 255.9 $^\circ\text{C}/\text{W}$
Junction-to-Case Thermal Resistance (θ_{JC}) 81 $^\circ\text{C}/\text{W}$

Thin μ DFN (Ultra-Thin LGA)

Junction-to-Ambient Thermal Resistance (θ_{JA}) 470 $^\circ\text{C}/\text{W}$

Note 1: Package thermal resistances were obtained using the method described in JEDEC specification JESD51-7, using a four-layer board. For detailed information on package thermal considerations, refer to www.maximintegrated.com/thermal-tutorial.

ELECTRICAL CHARACTERISTICS

($V_{DD} = 3.3$ V, $V_{SS} = 0$ V, $V_{IN+} = V_{IN-} = V_{DD}/2$, $R_L = 10\text{k}\Omega$ to $V_{DD}/2$, $V_{\overline{CAL}} = V_{\overline{SHDN}} = V_{DD}$, $T_A = -40^\circ\text{C}$ to +125 $^\circ\text{C}$. Typical values are at $T_A = +25^\circ\text{C}$, unless otherwise noted.) (Note 2)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
DC CHARACTERISTICS						
Input Voltage Range	V_{IN+} V_{IN-}	Guaranteed by CMRR test	-0.1	V_{DD} + 0.1		V
Input Offset Voltage (Note 3)	VOS	TA = +25 $^\circ\text{C}$		10	50	μV
		TA = -40 $^\circ\text{C}$ to +125 $^\circ\text{C}$ after calibration			100	
		TA = -40 $^\circ\text{C}$ to +125 $^\circ\text{C}$	MAX44260/MAX44261		500	
			MAX44259/MAX44263		800	
Input Offset Voltage Drift (Note 3)	VOS - TC	MAX44260/MAX44261		0.8	5	$\mu\text{V}/^\circ\text{C}$
		MAX44259/MAX44263		1	8	
Input Bias Current (Note 3)	IB	TA = +25 $^\circ\text{C}$	MAX44259/ MAX44260/MAX44261	0.01	0.5	pA
			MAX44263	0.01	0.5	
		TA = -40 $^\circ\text{C}$ to +85 $^\circ\text{C}$		10		
		TA = -40 $^\circ\text{C}$ to +125 $^\circ\text{C}$	MAX44259/ MAX44260/MAX44261		100	
			MAX44263		160	
Input Capacitance	CIN			0.4		pF
Common-Mode Rejection Ratio	CMRR	VCM = -0.1V to (V_{DD} + 0.1V)	75	90		dB

MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

ELECTRICAL CHARACTERISTICS (continued)

($V_{DD} = 3.3V$, $V_{SS} = 0V$, $V_{IN+} = V_{IN-} = V_{DD}/2$, $R_L = 10k\Omega$ to $V_{DD}/2$, $V_{CAL} = V_{SHDN} = V_{DD}$, $T_A = -40^\circ C$ to $+125^\circ C$. Typical values are at $T_A = +25^\circ C$, unless otherwise noted.) (Note 2)

PARAMETER	SYMBOL	CONDITIONS		MIN	TYP	MAX	UNITS
Open-Loop Gain	AOL	0.4V \leq VOUT \leq VDD - 0.4V, ROUT = $10k\Omega$	MAX44259/ MAX44260/MAX44261	100	115		dB
			MAX44263	97	115		
		0.4V \leq VOUT \leq VDD - 0.4V, ROUT = 600Ω	MAX44259/ MAX44260/MAX44261	91	100		
			MAX44263	86	100		
		0.4V \leq VOUT \leq VDD - 0.4V, ROUT = 32Ω			80		
Output Short-Circuit Current	ISC	To VDD or VSS		50		mA	
Output Voltage Swing	VOL - VSS	ROUT = $10k\Omega$		20			mV
		ROUT = 600Ω		50			
		ROUT = 32Ω		400	700		
	VDD - VOH	ROUT = $10k\Omega$	MAX44259/ MAX44260/MAX44261	10			
			MAX44263	10			
		ROUT = 600Ω	MAX44259/ MAX44260/MAX44261	40			
			MAX44263	50			
			ROUT = 32Ω	400		800	
AC CHARACTERISTICS							
Input Voltage-Noise Density	en	$f = 10\text{kHz}$		12.7		$\text{nV}/\sqrt{\text{Hz}}$	
Input Current-Noise Density	in	$f = 10\text{kHz}$		1.2		$\text{fA}/\sqrt{\text{Hz}}$	
Gain-Bandwidth Product	GBWP			15		MHz	
Slew Rate	SR			7		$\text{V}/\mu\text{s}$	
Settling Time		VOUT = 2VP-P, VDD = 3.3V, AV = 1V/V, CL = 30pF (load), settle to 0.01%		1.7		μs	
Capacitive Loading	CLOAD	No sustained oscillation		300		pF	
Total Harmonic Distortion	THD	$f = 10\text{kHz}$, VO = 2VP-P, AV = 1, ROUT = $10k\Omega$		-110		dB	
Output Transient Recovery Time		$\Delta\text{VOUT} = 0.2\text{V}$, VDD = 3.3V, AV = 1V/V; RS = 20Ω , CL = 1nF (load)		1		μs	
POWER-SUPPLY CHARACTERISTICS							
Power-Supply Range	VDD	Guaranteed by PSRR		1.8	5.5		V
		TA = $0^\circ C$ to $+70^\circ C$		1.7	5.5		
Power-Supply Rejection Ratio	PSRR	VCM = $V_{DD}/2$	MAX44259/MAX44260/ MAX44261	82	95		dB
			MAX44263	76	95		

MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

ELECTRICAL CHARACTERISTICS (continued)

($V_{DD} = 3.3V$, $V_{SS} = 0V$, $V_{IN+} = V_{IN-} = V_{DD}/2$, $R_L = 10k\Omega$ to $V_{DD}/2$, $V_{CAL} = V_{SHDN} = V_{DD}$, $T_A = -40^\circ C$ to $+125^\circ C$. Typical values are at $T_A = +25^\circ C$, unless otherwise noted.) (Note 2)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Quiescent Current	IDD	MAX44259/MAX44260/MAX44261	750	1200		μA
		MAX44263 (per amplifier)	650	1100		
Shutdown Supply Current	ISHDN	(Note 4)		1		μA
Shutdown Input Low	VIL	(Note 4)		0.5		V
Shutdown Input High	VIH	(Note 4)	1.3			V
Output Leakage Current in Shutdown	ISHDN	(Note 4)		100		pA
Shutdown Input Bias Current	IIL/IIH	MAX44260		1		μA
		MAX44261		0.1		
Shutdown Turn-On Time (Note 4)	tSHDN	TA = $+25^\circ C$ (Note 3)	14.4	18.9		μs
		TA = $-40^\circ C$ to $+125^\circ C$ (Note 3)	26.7			
Turn-On Time (Note 4)	tON	TA = $+25^\circ C$ (Note 3)	9.7	15.2		ms
		TA = $-40^\circ C$ to $+125^\circ C$ (Note 3)	18.4			




Note 2: All devices are 100% production tested at $T_A = +25^\circ C$. Temperature limits are guaranteed by design.

Note 3: Guaranteed by design.

Note 4: MAX44259/MAX44260/MAX44261 only.

Typical Operating Characteristics

($V_{DD} = 3.3V$, $V_{SS} = 0V$, $V_{IN+} = V_{IN-} = V_{DD}/2$, $R_L = 10k\Omega$ to $V_{DD}/2$, $V_{CAL} = V_{SHDN} = V_{DD}$, $T_A = -40^\circ C$ to $+125^\circ C$. Typical values are at $T_A = +25^\circ C$, unless otherwise noted. All devices are 100% production tested at $T_A = +25^\circ C$. Temperature limits are guaranteed by design.)









MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

Typical Operating Characteristics (continued)

($V_{DD} = 3.3V$, $V_{SS} = 0V$, $V_{IN+} = V_{IN-} = V_{DD}/2$, $R_L = 10k\Omega$ to $V_{DD}/2$, $V_{CAL} = V_{SHDN} = V_{DD}$, $T_A = -40^\circ C$ to $+125^\circ C$. Typical values are at $T_A = +25^\circ C$, unless otherwise noted. All devices are 100% production tested at $T_A = +25^\circ C$. Temperature limits are guaranteed by design.)












MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

Typical Operating Characteristics (continued)

($V_{DD} = 3.3V$, $V_{SS} = 0V$, $V_{IN+} = V_{IN-} = V_{DD}/2$, $R_L = 10k\Omega$ to $V_{DD}/2$, $V_{CAL} = V_{SHDN} = V_{DD}$, $T_A = -40^\circ C$ to $+125^\circ C$. Typical values are at $T_A = +25^\circ C$, unless otherwise noted. All devices are 100% production tested at $T_A = +25^\circ C$. Temperature limits are guaranteed by design.)









MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

Typical Operating Characteristics (continued)

($V_{DD} = 3.3V$, $V_{SS} = 0V$, $V_{IN+} = V_{IN-} = V_{DD}/2$, $R_L = 10k\Omega$ to $V_{DD}/2$, $V_{CAL} = V_{SHDN} = V_{DD}$, $T_A = -40^\circ C$ to $+125^\circ C$. Typical values are at $T_A = +25^\circ C$, unless otherwise noted. All devices are 100% production tested at $T_A = +25^\circ C$. Temperature limits are guaranteed by design.)








MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

Typical Operating Characteristics (continued)


($V_{DD} = 3.3V$, $V_{SS} = 0V$, $V_{IN+} = V_{IN-} = V_{DD}/2$, $R_L = 10k\Omega$ to $V_{DD}/2$, $V_{CAL} = V_{SHDN} = V_{DD}$, $T_A = -40^\circ C$ to $+125^\circ C$. Typical values are at $T_A = +25^\circ C$, unless otherwise noted. All devices are 100% production tested at $T_A = +25^\circ C$. Temperature limits are guaranteed by design.)



MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

Pin Configurations



Pin Description

PIN				NAME	FUNCTION
MAX44259	MAX44260	MAX44261	MAX44263		
3	1	1	—	IN+	Positive Input
2	2	2	4	VSS	Negative Power Supply. Bypass with a 0.1 μ F capacitor to ground.
4	3	3	—	IN-	Negative Input
1	4	4	—	OUT	Output
—	—	5	—	CAL	Active-Low Calibrate Input
—	5	—	—	SHDN	Active-Low Shutdown
5	6	6	8	VDD	Positive Power Supply. Bypass with a 0.1 μ F capacitor to ground.
—	—	—	1	OUTA	Channel A Output
—	—	—	2	INA-	Channel A Negative Input
—	—	—	3	INA+	Channel A Positive Input
—	—	—	5	INB+	Channel B Positive Input
—	—	—	6	INB-	Channel B Negative Input
—	—	—	7	OUTB	Channel B Output

MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

Detailed Description

The MAX44259/MAX44260/MAX44261/MAX44263 are high-speed low-power op amps ideal for signal processing applications due to the device's high precision and low-noise CMOS inputs. The devices self-calibrate on power-up to eliminate effects of temperature and power-supply variation.


The MAX44260 also features a low-power shutdown mode that greatly reduces quiescent current while the device is not operational and recovers in 30 μ s.

The MAX44261 features a user-selectable self-calibration input that shuts down the device and allows it to be recalibrated at any time. The calibration routine takes 10ms.


Crossover Distortion

These op amps feature a low-noise integrated charge pump that creates an internal voltage rail 1V above V_{DD}, which is used to power the input differential pair of PMOS transistors as shown in [Figure 1](#). Such a unique architecture eliminates crossover distortion common in traditional CMOS input architecture ([Figure 2](#)), especially when used in a noninverting configuration, such as for Sallen-Key filters.

The charge pump's operating frequency lies well above the unity-gain frequency of the amplifier. Thanks to its high-frequency operation and ultra-quiet circuitry, the charge pump generates little noise, does not require external components, and is entirely transparent to the user.



STANDARD INPUT STRUCTURE



MAX44260 INPUTS STRUCTURE

Figure 1. Comparing the Input Structure of the MAX44260 to Standard Op-Amp Inputs




Figure 2. Crossover Distortion of Typical Amplifiers

MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

Applications Information

Power-Up Autotrim

The ICs feature an automatic trim that self-calibrates the V_{OS} of these devices to less than $50\mu\text{V}$ of input offset voltage on power-up. This self-calibration feature allows the device to eliminate input offset voltage effects due to power supply and operating temperature variation simply by cycling its power. The autotrim sequence takes approximately 10ms to complete and is triggered by an internal power-on-reset (POR) circuitry. During this time, the inputs and outputs are put into high impedance and left unconnected. The MAX44261 can also be forced into a self-calibration cycle by pulling the $\overline{\text{CAL}}$ input low for $1\mu\text{s}$. This input also puts the part into shutdown mode.

Shutdown Operation

The MAX44260 features an active-low shutdown mode that puts both inputs and outputs into high impedance and substantially lowers the quiescent current to less than $1\mu\text{A}$. Putting the output into high impedance allows multiple outputs to be multiplexed onto a single output line without the additional external buffers. The device does not self-calibrate when exiting shutdown mode

and retains its power-up trim settings. [Figure 3](#) shows that the device also recovers from shutdown in under $30\mu\text{s}$.

The MAX44261 features a recalibrate input that acts the same as the shutdown mode of the MAX44260. However, when the input is pulled low, the device goes through a self-calibration sequence again ([Figure 3](#)).

The shutdown logic levels of the devices are independent of supply, allowing the shutdown feature of the device to operate off of a 1.8V or 3.3V microcontroller, regardless of supply voltage.

Rail-to-Rail Input/Output

The input voltage range of the ICs extends 100mV above V_{DD} and below V_{SS} . The wide input common-mode voltage range allows the op amp to be used as a buffer and as a differential amplifier in a wide-variety of signal processing applications. Output voltage high/low is designed to be only 50mV above V_{SS} and below V_{DD} allowing maximum dynamic range in single-supply applications. The high output current and capacitance drive capability of the devices make them ideal as an ADC driver and a line driver.




Figure 3. $\overline{\text{CAL}}$ vs. $\overline{\text{SHDN}}$ Input Operation

MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

Input Bias Current

The ICs feature a high-impedance CMOS input stage and a specialized ESD structure that allows low-input bias current operation at low-input, common-mode voltages. Low-input bias current is useful when interfacing with high-ohmic sensors. It is also beneficial for designing transimpedance amplifiers for photodiode sensors. This makes these devices ideal for ground-referenced medical and industrial sensor applications.

Active Filters

The MAX44259/MAX44260/MAX44261/MAX44263 are ideal for a wide variety of active filter circuits that make use of their wide bandwidth, rail-to-rail input/output stages and high-impedance CMOS inputs. The [Typical Application Circuit](#) shows an example Sallen-Key active filter circuit with a corner frequency of 10kHz. At low frequencies, the amplifier behaves like a simple low-distortion noninverting buffer, while its high bandwidth gives excellent stopband attenuation above its corner frequency. See the [Typical Application Circuit](#).

Driver for Interfacing with the MAX11645 ADC

The ICs' tiny size and low noise makes them a good fit for driving 12- to 16-bit resolution ADCs in space-constrained applications. The [Typical Application Circuit](#) shows the MAX44260 amplifier output connected to a lowpass filter driving the MAX11645 ADC. The MAX11645 is part of a family of 3V and 5V, 12-bit and 10-bit, 2-channel ADCs.

The MAX11645 offers sample rates up to 94ksps and measures two single-ended inputs or one differential input. These ADCs dissipate 670µA at the maximum sampling rate, but just 6µA at 1ksps and 0.5µA in shutdown. Offered in the ultra-tiny, 1.9mm x 2.2mm WLP and µMAX-8 packages, the MAX11645 ADCs are an ideal fit to pair with the MAX44260/MAX44261/MAX44263 amplifiers in portable applications.

Where higher resolution is required, refer to the MAX1069 (14-bit) and MAX1169 (16-bit) ADC families.

Chip Information

PROCESS: BiCMOS

Ordering Information

PART	TEMP RANGE	PIN-PACKAGE	TOP MARK
MAX44259AUK+	-40°C to +125°C	5 SOT23	+AMFX
MAX44260AXT+	-40°C to +125°C	6 SC70	+AEB
MAX44260AYT+	-40°C to +125°C	6 Thin µDFN (Ultra-Thin LGA)	+AY
MAX44261AXT+	-40°C to +125°C	6 SC70	+AEC
MAX44263AXA+	-40°C to +125°C	8 SC70	+AAG

+Denotes a lead(Pb)-free/RoHS-compliant package.

MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

Package Information

For the latest package outline information and land patterns (footprints), go to www.maximintegrated.com/packages. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

PACKAGE TYPE	PACKAGE CODE	OUTLINE NO.	LAND PATTERN NO.
5 SOT23	U5N+4	21-0057	90-0174
6 SC70	X6SN+1	21-0077	90-0189
6 Thin µDFN (Ultra-Thin LGA)	Y61A1+1	21-0190	90-0233
8 SC70	X8CN+1	21-0460	90-0348

MAX44259/MAX44260/MAX44261/MAX44263

1.8V, 15MHz Low-Offset, Low-Power, Rail-to-Rail I/O Op Amps

Revision History

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	6/11	Initial release	—
1	8/11	Added thin µDFN (ultra-thin LGA) package and updated slew rate and TOC 29	1, 2, 3, 8, 9, 12
2	10/11	Removed future product information from data sheet	12
3	2/12	Revised <i>Electrical Characteristics</i> and the <i>Power-Up Autotrim</i> section	2, 3, 11
4	7/12	Revised <i>Electrical Characteristics</i> and <i>Typical Operating Characteristics</i>	3, 6
5	10/12	Added the MAX44263 and revised the <i>Electrical Characteristics</i> , <i>Pin Description</i> , and <i>Pin Configuration</i> .	1–17
6	12/12	Revised <i>Typical Operating Characteristics</i>	7
7	9/14	Added the MAX44259 to data sheet.	1–14



Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the Electrical Characteristics table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.

Maxim Integrated 160 Rio Robles, San Jose, CA 95134 USA 1-408-601-1000

14

© 2014 Maxim Integrated Products, Inc. The Maxim logo and Maxim Integrated are trademarks of Maxim Integrated Products, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Maxim Integrated:

[MAX44260AXT+T](#) [MAX44261AXT+T](#) [MAX44260AYT+T](#) [MAX44261ASA+T](#) [MAX44261ASA+](#) [MAX44263AXA+T](#)
[MAX44260ASA+](#) [MAX44259AUK+](#) [MAX44260ASA+T](#) [MAX44259AUK+T](#)