




Home: Crimp Housings >

Part Number: 49615-0400

8.90mm Pitch MP-Lock™ Housing, 4 Circuits, PBT/PC UL94V-0, White



Series image - Reference only

Status:

OBsolete

Replacement:

Contact Molex

Series:

49615

Category:

Crimp Housings

Go to [Part Detail](#) ▾

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)[Email this page](#)

Use With Part(s):

[35068](#) MP-Lock™ Quick Disconnect**Product Environmental Compliance**[EU ELV](#):Product not active[EU RoHS](#):Product not active[EU RoHS Phthalates](#):Product not active[China RoHS](#):[REACH SVHC](#):Product not active[Low-Halogen Status](#):Product not active[EU RoHS Certificate of Compliance \(PDF\)](#)[Multiple Part Product Compliance Statements](#)

EU RoHS, REACH SVHC, & Low-Halogen

[Multiple Part Industry Compliance Documents](#)

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail**[COLLAPSE ALL](#)

▼ General

Status	Obsolete
Category	Crimp Housings
Series	<u>49615</u>
Application	Power
Comments	Polarized to mating part
Product Name	MP-Lock™
UPC	883906024994

▼ Physical

Breakaway	No
Circuits (maximum)	4
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester Alloy
Net Weight	4.009/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	8.90mm
Pitch - Termination Interface	8.90mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +105°C

▼ Electrical

(Please review the Product Specification for specific details.)	
Current - Maximum per Contact	12.0A

PRODUCTS**QUICK LINKS****RESOURCES****STAY CONNECTED**

Antennas

Company Information

Supply Chain Transparency



Application Tooling

Contact Molex

Business Continuity



Cable Assemblies

Cross-Reference

Compliance



Connected Lighting

Koch Industries

Feedback | Help



Connectors

Industries

Jobs



Copper Flex

Investor Relations

Legal | Trademarks



Electrical Products

Literature

Mobile Site



Industrial Automation

Molex Racing

Supplier Portal



Membrane Switches

Press Room / Press Releases

Privacy Policy



Optical Solutions

Product Index

Tradeshows



Printed Electronic Solutions

Sitemap

Tradeshows



Terms & Conditions

Tradeshows

Terms & Conditions