



止め金付キースイッチ

KEYSWITCHES WITH STOPPER PLATES

特 徴 Feature

- キースイッチに止め金を付属したロック機構付キースイッチです。
- 止め金の動作とスイッチの動作を同時に行います。
- 錠前部分C-88-5タイプ使用。鍵違い最大数6,000通り
- 反転スイッチ機構
- Lock mechanism keyswitch: stopper plate is attached to keyswitch.
- Stopper plate and switch operations are performed simultaneously.
- Lock is C-88-5 type. Key differences: max. 6,000 sets.
- Reversible switch mechanism.

- 仕 様
- 製品質量: 65g
 - 材 質: 本体/快削黄銅棒 (C3602)
亜鉛合金 (ZDC)
キー/冷間圧延鋼板 (SPCC)
快削鋼材 (SUM)
 - 表面仕上: 本体/クロムめっき (MBCr)
亜鉛めっきクロメート処理 (MZZn-C)
キー/ニッケルめっき (MFNi)

- 用 途
納 期
ス イ ッ チ
特 性
- 鍵 番 号: M0020
 - 同一鍵番号・鍵違いがあります。
 - 付 属 品: キー2本
 - コンピュータ・電源装置
 - 標準在庫品
 - 定 格: AC125V・3A (抵抗負荷)
DC30V・3A (抵抗負荷)
最小適用負荷: DC5V・100mA (抵抗負荷)
 - 接触抵抗: 20mΩ以下 (初期値)
 - 絶縁抵抗: 100MΩ以上 (500VDC)
 - 耐 電 圧: (50/60Hz, 1分間)
非連続端子 AC1000V
各端子と非充電金属部間 AC1500V
 - 耐 久 性: 機械的3万回以上
電氣的1.5万回以上
 - 接点素材: 銀めっき
 - 使用周囲温度: -20～+70℃ (氷結しないこと)
 - 使用周囲湿度: 85%RH以下 (結露しないこと)
 - 耐 振 動: 10～55Hz 複振幅1.5mm
 - 耐 衝 撃: 30G以上
 - 施解錠は錠前の構造上、鍵を押しながら回してください。

- 備 考
- Mass: 65g
 - Material: Main body: Free cutting brass bar (C3602)
Zinc alloy (ZDC)
Key: Cold rolled steel plate (SPCC)
Free cutting steel (SUM)
 - Finish: Main body: Chrome plating (MBCr)
Zinc plating chromate treatment (MZZn-C)
Key: Nickel plating (MFNi)

- Specific use
Switch
characteristic
- Key No.: M0020
 - Keyed alike and key differences are available.
 - Accessories: Two keys
 - Computers and power supplies
 - Rated: AC125V・3A (resistanced load)
DC30V・3A (resistanced load)
Min. applicable load: DC5V・100mA (resistanced load)
 - Contact resistance: 20mΩ or less
 - Insulation resistance: 100MΩ or more (500VDC)
 - Withstand voltage: (50/60 Hz, one minute)
Between non-continuous terminals: AC1000V
Between each terminal and non-charged metal: AC1500V
 - Durability: Mechanical: 30,000 times or more
Electrical: 15,000 times or more
 - Contact material: Silver plating
 - Ambient temperature: -20°C to +70°C (non-freezing)
 - Operating humidity range: 85%RH or less (non-condensing)
 - Vibration resistance: 10 to 55Hz
multiple-amplitude 1.5mm
 - Impact resistance: 30G or more
 - Due to the structure of the lock, the key must be pushed in as it is turned in order to release the lock.

Remarks



S-28-90-BC-1



キーNo.M0020
Key





商品番号 Product No.	RoHS 10	CAD	コード Code	単 価 Price	量販価格 Bulk Price 数量 Quantity 単価 Price
S-28-90-B-1 同番 Keyed alike			40188	¥2,600	5個～ ¥2,496
S-28-90-B-1 鍵違い Key differences			40189	¥2,700	5個～ ¥2,592
S-28-90-B-2 同番 Keyed alike		3D	40235	¥2,650	5個～ ¥2,544
S-28-90-B-2 鍵違い Key differences		3D	40236	¥2,750	5個～ ¥2,640
S-28-90-BC-1 同番 Keyed alike			40190	¥2,650	5個～ ¥2,544
S-28-90-BC-2 同番 Keyed alike		2D	40237	¥2,750	5個～ ¥2,640

●: RoHS10指令対応品 ※大量のご注文は更にお安くなります。
▲: RoHS10指令に対応可能です。

接点構成表

Position of mark (●) shows that key can be inserted/removed.

商品番号 Product No.	鍵回転角度 Key turning angle	B 位置 B position	C 位置 C position
S-28-90-B-1 (1回路2接点型) (one-circuit-two-contact)	90° B位置 B position C位置 C position	SW COM NO NC	SW COM NO NC
S-28-90-BC-1 (1回路2接点型) (one-circuit-two-contact)	90° B位置 B position C位置 C position	SW COM NO NC	SW COM NO NC
S-28-90-B-2 (2回路2接点型) (two-circuit-two-contact)	90° B位置 B position C位置 C position	SW1 COM NO NC SW2 COM NO NC	SW1 COM NO NC SW2 COM NO NC
S-28-90-BC-2 (2回路2接点型) (two-circuit-two-contact)	90° B位置 B position C位置 C position	SW1 COM NO NC SW2 COM NO NC	SW1 COM NO NC SW2 COM NO NC



パネル穴明け寸法 Panel drilling dimensions

