



HONEYWELL PART NUMBER
11SM303-T2
PRODUCT CODE TWW9990

REV	DOCUMENT	CHANGED BY	CHECK
9	0038104	PK 23APR08	ASD



PLASTIC PLUNGER



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 400°F
 - 4 - MATING CONTACT SURFACES ARE 24K SOLID GOLD OVERLAY

RELEASE NO.	PR-2645
REPLACES	-

CHARACTERISTICS	ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± ANGLES ±			DRAWN	VK	27 NOV 07	Honeywell			
OPERATING FORCE — — — — 3 - 5 OZ	CONTACT ARRANGEMENT SPDT						CHECK	RJ	27 NOV 07				
RELEASE FORCE — — — — 1 OZ MIN	30 VOLTS DC RATING						THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC			
		SEA LEVEL	50,000 FT										
DIFFERENTIAL TRAVEL — — — .004 MAX	INDUCTIVE	1/2 AMP	1/2 AMP										
OVERTRAVEL — — — — — .005 MIN	RESISTIVE	1 AMP	1 AMP										
MAXIMUM INRUSH 2 AMP				THIRD ANGLE PROJECTION 			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME	REV
APPROVALS KEMA, CE 1A, 250V ~ T85 1E4  UL, CSA 1A, 125 VAC   BRAND L 22							B			I	11SM303-T2	9	
							RASTER			SCALE -	WEIGHT .006 LB	SHEET 1 OF 1	