











spec ref -			dr GL L00		2006-05-23		projection				size A3		scale 3:1			
tolerance std ISO 406 ISO 1101 TOLERANCES UNLESS OTHERWISE SPECIFIED			eng GL L00		2006-05-23						ecn no S10-0228					
			chr GL L00		2010-10-28											
			appr JOEY NG		2010-10-28						product family SAS		rel level -			
surface - ✓ ISO 1302			linear		0.X		± -				title SAS CABLE RECEP CONNECTOR -		dwg no 10054542		rev B	
					0.XX		±0.20									
					0.XXX		± -									
			angular		0°		±2°									

NOTES:

1. THIS PRODUCT MEETS THE SAS SPEC REV 1.7
2. MATERIAL :
1) HOUSING : HIGH TEMP. THERMOPLASTIC, UL 94V-0
COLOR : BLACK
2) TERMINAL : COPPER ALLOY
3. FINISH :
1) TERMINAL : 3μ" Au PLATING (CONTACT POINT)
OVER 50μ" MIN NICKEL
2) SOLDER TAIL : 50μ" MIN TIN OVER 50μ" MIN NICKEL
4. TRUE POSITION NOTES APPLY AT TERMINAL TIP
- ⑤ COVER :
MATERIAL : THERMOPLASTIC,
THK = 0.8mm REF
6. THE STD PACKAGING IS IN TRAY.
7. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH 1.57MM THICK CIRCUIT BOARD.
- ⑧ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ⑨ PART NUMBERS ENDING IN "LF" MEANS FOR NOTE ⑧ LEAD FREE IDENTIFICATION.
- ⑩ MEASURED AT DATUM C
- ⑪ A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

spec ref -				dr	GL L00	2006-05-23	projection 	MM 	size	A3	scale	3:1
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	GL L00	2006-05-23			ecn no S10-0228			
				chr	GL L00	2010-10-28			rel level -			
				appr	JOEY NG	2010-10-28						
surface  ISO 1302	linear	0.X	± -		title -	SAS CABLE RECEP CONNECTOR	dwg no	10054542		rev B		
		0.XX	±0.20									
		0.XXX	± -									
	angular	0°	±2°	www.fci.com	cat. no.	-	Product - Customer Drw		sheet 2 of 2			