

Customer Information Sheet

DRAWING No.: M80-FC1305FI-XX-XXXXL


IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



SPECIFICATIONS:

MATERIAL:
MOULDING: GLASS FILLED PPS,
UL94V-0, BLACK

COAX CONTACT:
BODY, SLEEVE, INNER CONTACT,
END PLUG = COPPER ALLOY
LATCHING COLLAR = BERYLLIUM COPPER
INSULATOR = PTFE

FINISH:
COAX CONTACT:
BODY, SLEEVE, INNER CONTACT,
END PLUG = GOLD
LATCHING COLLAR = NICKEL

ELECTRICAL:
WORKING VOLTAGE = 800V AC/DC
VOLTAGE PROOF = 1200V AC/DC
INSULATION RESISTANCE = 100MΩ MIN

COAX CONTACT:
FREQUENCY RANGE = 6GHz
IMPEDANCE = 50Ω
V.S.W.R =
1.05 + (0.04 x FREQUENCY) GHz MAX
CONTACT RESISTANCE = 6mΩ MAX

INSULATION RESISTANCE = 10⁶MΩ @250V AC
OPERATING VOLTAGE = 180V AC @ 500mA
MAXIMUM VOLTAGE = 1000V AC

MECHANICAL:
DURABILITY = 500 OPERATIONS

COAX CONTACT:
INSERTION FORCE = 8N MAX
WITHDRAWAL FORCE = 0.5N MIN

ENVIRONMENTAL:
TEMPERATURE RANGE = -55°C TO +125°C

PACKING:
BAG
FOR COMPLETE SPECIFICATION SEE COMPONENT
SPECIFICATION C005XX (LATEST ISSUE)

DIMENSION	MEASUREMENT
DIM 'A'	4 x TOTAL No. OF CONTACTS + 5.00
DIM 'B'	4 x TOTAL No. OF CONTACTS - 4.00
DIM 'D'	4 x TOTAL No. OF CONTACTS + 10.00
EXAMPLE PART No.: CONNECTOR WITH 6 CONTACTS AND 150mm OF WIRE = M80-FC305FI-06-0150L CONNECTOR WITH 2 CONTACTS AND 450mm OF WIRE = M80-FC305FI-02-0450L	

NOTES:
1. CABLE ASSEMBLIES WILL BE PACKED IN BAGS OF 10.

ORDER CODE:	M80-FC305FI-XX-XXXXL
TOTAL No. OF CONTACTS:	02, 04, 06, 08
DIM 'C' LENGTH:	0060 = 60mm MIN 9999 = 9999mm MAX
STOCKED LENGTH:	0150 = 150mm

MSP	2	17.08.17	20748
NAME	ISS.	DATE	C/NOTE
APPROVED: M.PERREN			
CHECKED: M.PLESTED			
DRAWN: M.PERREN			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE:
DATAMATE COAX FEMALE TO
FEMALE CABLE ASSEMBLY

DRAWING NUMBER:
M80-FC305FI-XX-XXXXL

SHT
2 OF 2