


PRODUCT NO.	DIM A	DIM L	DIM B
50272-001	.320/8.13	.560/14.22	.227/5.77
50272-002	.389/9.88	.628/15.95	.296/7.52
50272-003	.458/11.63	.697/17.7	.365/9.27



NOTES:

- MATERIAL: BRASS
- PLATING:
 ZONE A: 100u"/2.54u MIN SnPb. AT SUPPLIER'S DISCRETION, 100u"/2.54u MIN. Sn MAY BE SUBSTITUTED.
 ZONE B: 30u"/.76u MIN Au OVER
 UNDERPLATE: 50u"/1.27u MIN Ni
- VARIATIONS SHOWN ON THIS PRINT ARE "STANDARD" PIN LENGTHS. SEE P/N 91279 FOR "SPECIAL" PIN LENGTHS.
- ALL UNSPECIFIED ANGLES TO BE 45°.
- SURFACE FINISH IN CONTACT AREA (ZONE "B") .050) SHOULD NOT EXCEED 25rms.

mat'l. code				surface ISO 1302 ☒	tolerance ISO 406 ISO 1101	projection 	product family HPC
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 1:1	title POWER PIN SOLDER TAIL
C	V31883	GIP	10/28/93	angles	.XX $\pm$.01/.3		
D	V32161	PDP	12/7/93	linear	.XXX $\pm$.005/.13	FCI	dwg no 50272
E	V40377	MDF	2/15/94	0' $\pm$ 2'	.XXXX $\pm$.0020/.051		
F	V40764	PDP	4/14/94	dr	S. SHEAFFER	3/27/92	sheet 1 of 1 size A3
G	C70024	MSC	2/28/97	enr	S. CLARK	4/28/92	
H	V00558	LSS	3/3/00	chr	S. CLARK	4/28/92	type Product Customer Drawing
J	M06-0265	AGS	7/10/06	appd	S. CLARK	4/28/92	
sheet index	revision	J					
	sheet	1					

form: A3