

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

FT

0




B

REVISED PER 0G3B-0119-01

06FEB2002


EZ

DB



284515-3 AS SHOWN

87.5	25	2-284515-5
84.0	24	2-284515-4
80.5	23	2-284515-3
77.0	22	2-284515-2
73.5	21	2-284515-1
70.0	20	2-284515-0
66.5	19	1-284515-9
63.0	18	1-284515-8
59.5	17	1-284515-7
56.0	16	1-284515-6
52.5	15	1-284515-5
49.0	14	1-284515-4
45.5	13	1-284515-3
42.0	12	1-284515-2
38.5	11	1-284515-1
35.0	10	1-284515-0
31.5	9	284515-9
28.0	8	284515-8
24.5	7	284515-7
21.0	6	284515-6
17.5	5	284515-5
14.0	4	284515-4
10.5	3	284515-3
7.0	2	284515-2
DIM A	NO OF POS	PART NUMBER



MATERIALS AND FINISH

HOUSING : PA 6.6, UL 94-V0, COLOR GREEN
TERMINAL : PHOSPHOR BRONZE, TIN PLATED


2 END-TO-END STACKABLE W/INTERLOCK WITHOUT
LOSS OF CENTERLINE SPACING

3 SUITABLE FOR 1.6-2.4 mm. PC BOARD THICKNESS



4 NOT CUMULATIVE TOLERANCE

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±.3
1 PLC ±.3
2 PLC ±.25
3 PLC ±.
4 PLC ±.
ANGLES ±2

MATERIAL



FINISH



DWN 06FEB2002

E. ZANOLINI

CHK 06FEB2002

E. ZANOLINI

APVD 06FEB2002

D. BIEVENOUR

PRODUCT SPEC

108-20166

APPLICATION SPEC

114-20079

WEIGHT -

CUSTOMER DRAWING

BUCHANAN

Tyco Electronics
Harrisburg, PA 17105-3608

NAME
TERMINAL BLOCK, HEADER ASSEMBLY
STRAIGHT, OPEN ENDS
STACKING W/INTERLOCK, 3.5mm PITCH

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-284515

SCALE 4:1 SHEET 1 OF 1 REV B