

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOCAD

DIST00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	AM3	REVISED PER ECO-11-004587	11MAR11	RK	HMR

1. FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7532.

2. SWITCH SHOWN IN OPEN POSITION.

3. ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLUE.

4. STAMPING WILL VARY ON 2 AND 3 POSITION SIDES DUE TO SPACE RESTRICTIONS.

5

.315 DIMENSION APPLIES AT TERMINAL TIPS.

TERMINALS ARE .300^{+.010}-.000 AT MOUNTING SURFACE.

6

STRIPPABLE TRANSPARENT SEAL, SEE FIG 1.

7	OBSOLETE	FIG 6	-----	1.08	10	6-435640-1	
			-----	.58	5	6-435640-0	
7	OBSOLETE	FIG 7	-----	.48	4	5-435640-9	
			-----	.88	8	5-435640-8	
			-----	.98	9	5-435640-7	
7	OBSOLETE	FIG 5	6	.68	6	5-435640-6	
				.58	5	5-435640-5	
				.48	4	5-435640-4	
		FIG 2	6	.88	8	5-435640-3	
	OBSOLETE	FIG 5	6	.88	8	5-435640-2	
				1.08	10	5-435640-1	
		FIG 3	6	.88	8	5-435640-0	
				.88	8	4-435640-9	
				.58	5	4-435640-8	
7	SUPSD BY 4-5435640-8	NONE	-----	1.08	10	4-435640-7	
				1.28	12	4-435640-3	
				1.08	10	4-435640-1	
				.98	9	4-435640-0	
				.88	8	3-435640-9	
				.78	7	3-435640-8	
				.68	6	3-435640-7	
				.58	5	3-435640-6	
				.48	4	3-435640-5	
				.38	3	3-435640-4	
				.28	2	3-435640-3	
	SUPSD BY 3-435668-3	FIG 4	-----	1.28	12	3-435640-2	
	SUPSD BY 2-435668-6 3-1589670-4		-----	.38	3	3-435640-0	
			-----	.28	2	2-435640-9	
		OBSOLETE	FIG 2	-----	.78	7	2-435640-2
				1.08	10	435640-7	
				.98	9	435640-6	
				.88	8	435640-5	
				.68	6	435640-4	
				.58	5	435640-3	
				.48	4	435640-2	
				.78	7	435640-1	
		TOP MARKING	PROTECTIVE SEAL	A	NO OF POSN	PART NO.	

435640-4 SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	.005
4 PLC	±	-
ANGLES	±	-

MATERIAL

HOUSING & ROCKERS; POLYESTER
CONTACTS; COPPER ALLOY

FINISH

CONTACTS; PLATED .000030 MIN
GOLD IN CONTACT AREA OVER
.000050 MIN NICKEL

DWN15NOV89

R.TALLEY

CHK06MAR90

R.L.MILLER

APVD06MAR90

H.LEITER

PRODUCT SPEC

APPLICATION SPEC

WEIGHT-

CUSTOMER DRAWING

TE Connectivity

NAME

SWITCH ASSY, DIP, TYPE C,
7100 SERIES, SPST, STANDARD

SIZEA2

CAGE CODE00779

DRAWING NOC=435640

RESTRICTED TO-

SCALE4:1

SHEET1 of 1

REVAM3

FIG 1

FIG 2

FIG 3

FIG 4

FIG 5

FIG 6

FIG 7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI