



# Ty-Rap®

## Standard T&B Catalog Number:

TY26MX

78621083987

Status:

Active

Description:

Cable Tie 40lb 11" Ultraviolet Resistant Black Nylon with Stainless Steel Locking Device Bulk Pack

## Features

Oval low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time. Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The Turned-up Tail orients the tie for easy assembly, making the ties easier to pick up on a flat surface. The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

## General

Material	Nylon 6.6 Weather Resistant
Color	Black

## Dimension Information

Nominal Length (inches)	11
Length (inches)	11.1
Width (inches)	.140
Max. Wire Bundle Diameter (inches)	3

## Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

## Tooling

Application Tools	ERG50, WT1-TB
-------------------	---------------

## Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
Package Type	Bulk
T&B Sold in UOM	Each

T&B Weight Per UOM 0.28 lbs. per 100

**Application Support**

Overview Available on Website

Material Selection Guide Available on Website

Available Colors Available on Website

**Certifications**

RoHS Compliance Yes

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:[techsupport@tnb.com](mailto:techsupport@tnb.com)