

Soft Recovery Rectifier



Features:

- High surge current capability
- Void-free plastic package
- 2 Ampere operation at $T_A = 55^\circ\text{C}$ with no thermal runaway
- Fast switching for high efficiency
- Exceeds environmental standards of MIL-S-19500/228

Mechanical Data:

Case	: Moulded plastic DO-201AD
Terminals	: Axial leads, solderable per MIL-STD-202, Method 208
Polarity	: Band denotes Cathode end
Mounting position	: Any
Weight	: 0.04oz, 1.1g

Max. Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Parameter	Symbols	BY299	Units
Max. recurrent peak reverse voltage	V_{RRM}	800	V
Max. RMS voltage	V_{RMS}	560	
Max. DC blocking voltage	V_{DC}	800	
Max. average forward rectified current 0.375" (9.5mm) lead length at $T_A = 55^\circ\text{C}$	$I_{(AV)}$	2	A
Peak forward surge current 10ms single half sine-wave superimposed on rated load	I_{FSM}	70	
Max. repetitive peak forward surge (Note 1)	I_{FRM}	10	
Max. instantaneous forward voltage at 3A	V_F	1.3	V
Max. DC reverse current $T_A = 25^\circ\text{C}$ at rated DC blocking voltage $T_A = 100^\circ\text{C}$	I_R	10 500	μA
Max. reverse recovery time (Note 3) $T_J = 25^\circ\text{C}$	T_{RR}	150	ns
Typical junction capacitance (Note 2) $T_J = 25^\circ\text{C}$	C_J	28	pF
Typical thermal resistance (Note 4)	$R_{\theta JA}$	15	$^\circ\text{C/W}$
Operating temperature range	T_J	-50 to +125	$^\circ\text{C}$
Storage temperature range	T_{STG}	-50 to +150	

Notes:

1. Repetitive peak forward surge current at $f < 15\text{kHz}$.
2. Measured at 1MHz and applied reverse voltage of 4V.
3. Reverse recovery test conditions: $I_F = 0.5\text{A}$, $I_R = 1\text{A}$, $I_{rr} = 0.25\text{A}$.
4. Thermal resistance from junction to ambient at 0.375" (9.5mm) lead length with both leads to heat sink.

Rating and Characteristics Curves




Figure 1 - Forward Current Derating Curve








Figure 2 - Maximum Non-Repetitive Peak Forward Surge Current





Dimensions

DO-201AD



Dimensions : Millimetres

Part Number Table

Description	Part Number
Diode, Fast, 2A, 800V	BY299

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.