


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		H2	REVISED PER ECO-11-004820	11MAR11	RK	HMR

D



- 1

0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
- 2

WIRE RANGE: 0.12–0.4mm² (26–22 AWG).
- 3



INSULATION RANGE: 1.20–1.75 [.047–.069] DIA.
- 4

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5


0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
- 6

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

C



B



6	OBSOLETE	5	0.20 [.008] PH BRZ	4-770986-1
		5	0.20 [.008] BRASS	1-770986-0
		1	0.20 [.008] BRASS	770986-3
	PRE-TIN		0.20 [.008] BRASS	770986-1
	FINISH		MATERIAL	PART NUMBER

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	0.15[.006]
4 PLC	±	-
ANGLES	±	1°

FINISH
SEE TABLE

DWN
S. HOOVER
18OCT02

CHK
C. JONES
18OCT02

APVD
C. JONES
18OCT02

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
SOCKET, LOOSE PIECE,
MINI UNIVERSAL MATE-N-LOK(TM)

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=770986

RESTRICTED TO
-

SCALE
10:1

SHEET
1 OF 1

REV
H2