

PRODUCT NUMBER

XXXXX-YYY HLF


LEAD FREE OPTION
SEE NOTE 1,7

HIGH TEMPERATURE PLASTIC
SEE NOTE 1


NO. OF
POSITIONS
SEE NOTE 1

PIN PLATING
SEE SHEET 2


BASE PART NO.



TOP VIEW



SIDE VIEW



END VIEW

⌀ .020/0.51 (M) U (M) V (S)

NOTE 4

□ .025±.001
0.64±0.03
TYP

□ .013
0.33 MAX TYP

25°±5°TYP
4 SIDES


DETAIL P
TYP BOTH ENDS

rev	ecn no	dr	date
CX	ELX-N-16105	ZK	2013-10-22
CS	N06-0165	MHT	7/04/06
CT	M06-0269	AEA	7/14/06
CU	M06-0307	MHT	8/08/06
CV	M08-0291	MHT	10/08/08
CW	N11-0118	J.Z	2011-04-13

www.fciconnect.com			surface 6.4 ISO 1302	tolerance std ISO 406 ISO 1101	projection A4	INCH/MM Scale 1.000
Dr	T. BREWBAKER	1/31/95	ANGULAR	0.X	±0.3	size
Eng	T. HANNA	1/31/95	LINEAR	0.XX	±0.15	ECN
Chr	T. HANNA	1/31/95	0° ±2°	0.XXX	±0.05	Spec ref
Appr	T. HANNA	1/31/95	Product family	BERGSTIK	dwg no 78563	
title			BERGSTIK® II HDR, D/R .100 CTR, R.R. TRACK			Rev. CX
catalog no			CUSTOMER			sheet 1 of 7

PIN PLATING CODES:

XXXXX-1YY	30u"/0.76u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-2YY	15u"/0.38u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-3YY	50u"/1.27u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-4YY	TIN LEAD OPTION 120u"/3.05u MIN 93/7 SnPb OVER 50u"/1.27u MIN Ni
	LF OPTION 100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 1,9)
XXXXX-5YY	15u"/0.38u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-6YY	30u"/0.76u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-7YY	30u"/0.76u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-8YY	15u"/0.38u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-9YY	15u"/0.38u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-0YY	30u"/0.76u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni

DOUBLE ROW
RECOMMENDED HOLE PATTERN

NOTES

1. PART NUMBER OPTIONS:

PIN PLATING CODES (SEE ABOVE)

HIGH TEMP. MATERIAL:

FOR HIGH-TEMPERATURE APPLICATIONS, SPECIFY AN 'H' AT THE END OF THE PART NUMBER, AND PCT WILL BE SUPPLIED.

NUMBER OF POSITION:

ANY NUMBER OF POSITIONS FROM 4 (2X2) THRU 72 (2X36).

PACKAGING:

PACKAGED IN POLY BAGS.

LEAD FREE:

ADD 'HLF' SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION, NOT AVAILABLE FOR -5YY, -5YYH, -6YY & -6YYH.

2. BODY MATERIAL:

MANUFACTURER'S OPTION OF NYLON OR PCT, GLASS FIBER REINFORCED, FLAME RETARDANT PER UL-94V-0.

COLOR: BLACK OR

MINERAL FILLED LCP FLAME RETARDANT PER UL-94V-0.

COLOR: BLACK

PART NUMBERS WITH 'H' SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT 'H' SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.

3. PIN MATERIAL: PHOS-BRONZE.

4. MEASURED WITH PART IN RESTRAINED CONDITION.

5. TWO SIDES OF PIN TIPS NOT PLATED. TYPICAL BOTH ENDS.

6. 2LBS/0.9KG MIN PIN RETENTION IN EITHER DIRECTION.

7. THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

8. PLATING OPTIONS:

PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON POST OR TAIL, OPTIONALLY (78~295u"/2~7.5u) TIN ON TAIL.

9. THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS.

www.fciconnect.com			surface ISO 1302 ✓	tolerance std ISO 406 ISO 1101	projection INCH/MM	INCH/MM	
			TOLERANCES UNLESS OTHERWISE SPECIFIED		size	A4	
Dr	T. BREWBAKER	1/31/95	ANGULAR	LINEAR	0.X	±0.3	Scale
Eng	T. HANNA	1/31/95			0.XX	±0.15	1.000
Chr	T. HANNA	1/31/95	0°	±2°	0.XXX	±0.05	ECN
Appr	T. HANNA	1/31/95	Product family			Spec ref	
			title			dwg no	Rev.
			BERGSTIK® II HDR. D/R			78563	CX
			catalog no			CUSTOMER	sheet 2 of 7

1

2

3

4

A

B

C

D

A

B

C

D

PRODUCT NUMBER	TOTAL PIN LGTH		TAIL LENGTH		MATING LENGTH		HEIGHT ABOVE BOARD		LF OPTION
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	DIM J	DIM J	
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	
58478-XXYH	0.808	20.52	0.120	3.05	0.268	6.81	0.420	10.67	OB
58479-XXYH	1.030	26.16	0.200	5.08	0.360	9.14	0.470	11.94	OB
60056-XXYH	0.425	10.80	0.150	3.81	0.065	1.65	0.210	5.33	OB
71282-XXYH	0.543	13.79	0.102	2.59	0.213	5.41	0.228	5.79	OB
71284-XXYH	0.920	23.37	0.122	3.10	0.372	9.45	0.426	10.82	OB
71285-XXYH	1.075	27.31	0.110	2.79	0.350	8.89	0.615	15.62	OB
71704-XXYH	1.145	29.08	0.354	8.99	0.354	8.99	0.437	11.10	OB
71725-XXYH	1.110	28.19	0.110	2.79	0.370	9.40	0.630	16.00	OB
71726-XXYH	1.380	35.05	0.315	8.00	0.315	8.00	0.750	19.05	OB
71728-XXYH	1.200	30.48	0.100	2.54	0.254	6.45	0.846	21.49	OB
71739-XXYH	0.945	24.00	0.110	2.79	0.110	2.79	0.725	18.42	OB
71741-XXYH	1.340	34.04	0.110	2.79	0.330	8.38	0.900	22.86	OB
71758-XXYH	1.123	28.52	0.394	10.01	0.394	10.01	0.335	8.51	OB
71797-XXYH	0.705	17.91	0.125	3.18	0.240	6.10	0.340	8.64	OB
72302-XXYH	1.176	29.87	0.100	2.54	0.230	5.84	0.846	21.49	OB
72307-XXYH	0.880	22.35	0.250	6.35	0.330	8.38	0.300	7.62	NOTE 1,7
72334-XXYH	0.775	19.69	0.120	3.05	0.230	5.84	0.425	10.80	OB
72335-XXYH	1.250	31.75	0.120	3.05	0.230	5.84	0.900	22.86	OB
72345-XXYH	0.630	16.00	0.100	2.54	0.230	5.84	0.300	7.62	OB
72320-XXYH	1.158	29.41	0.100	2.54	0.290	7.37	0.768	19.51	OB
72431-XXYH	1.150	29.21	0.262	6.65	0.262	6.65	0.626	15.90	OB
72461-XXYH	1.190	30.23	0.090	2.29	0.350	8.89	0.750	19.05	OB
72471-XXYH	1.286	32.66	0.130	3.30	0.406	10.31	0.750	19.05	OB
72509-XXYH	1.370	34.80	0.235	5.97	0.235	5.97	0.900	22.86	OB
72514-XXYH	1.220	30.99	0.120	3.05	0.350	8.89	0.750	19.05	OB
72521-XXYH	0.900	22.86	0.200	5.08	0.300	7.62	0.400	10.16	OB
73428-XXYH	1.330	33.78	0.330	8.38	0.727	18.47	0.273	6.93	OB
73500-XXYH	0.870	22.10	0.300	7.62	0.300	7.62	0.270	6.86	OB

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection A4		INCH/MM ←→	
			TOLERANCES UNLESS OTHERWISE SPECIFIED				size		Scale	
Dr	T. BREWBAKER	1/31/95	ANGULAR		LINEAR		0.X ±0.3		A4 1.000	
Eng	T. HANNA	1/31/95					0.XX ±0.15			
Chr	T. HANNA	1/31/95	0° ±2°				0.XXX ±0.05		ECN	
Appr	T. HANNA	1/31/95	Product family				BERGSTIK		Spec ref	
FCI			title				BERGSTIK® II HDR, D/R		dwg no	
							.100 CTR, R.R. TRACK		78563	
			catalog no				CUSTOMER		Rev. CX	
									sheet 3 of 7	

1

2

3

PDS: Rev :CX

STATUS:Released

Printed: Oct 29, 2013

1

2

3

4

A

B

C

D

A

B

C

D

PRODUCT NUMBER	TOTAL PIN LGTH		TAIL LENGTH		MATING LENGTH		HEIGHT ABOVE BOARD		LF OPTION
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	DIM J	DIM J	
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	
73501-XYH	0.668	16.97	0.098	2.49	0.157	3.99	0.413	10.49	OB
73697-XYH	1.435	36.45	0.300	7.62	0.525	13.34	0.610	15.49	OB
73699-XYH	0.952	24.18	0.122	3.10	0.228	5.79	0.602	15.29	OB
74381-XYH	0.975	24.77	0.360	9.14	0.360	9.14	0.255	6.48	OB
74455-XYH	1.050	26.67	0.230	5.84	0.320	8.13	0.500	12.70	OB
74465-XYH	0.945	24.00	0.110	2.79	0.285	7.24	0.550	13.97	OB
74466-XYH	0.930	23.62	0.355	9.02	0.360	9.14	0.215	5.46	OB
74467-XYH	0.930	23.62	0.365	9.27	0.365	9.27	0.200	5.08	OB
74928-XYH	1.164	29.56	0.200	5.08	0.200	5.08	0.764	19.41	OB
74997-XYH	1.208	30.68	0.150	3.81	0.290	7.37	0.768	19.51	OB
78563-XY	0.930	23.62	0.340	8.64	0.340	8.64	0.250	6.35	OB
78564-XY	1.230	31.24	0.390	9.91	0.390	9.91	0.450	11.43	OB
78936-XY	0.785	19.94	0.120	3.05	0.120	3.05	0.545	13.84	OB
78937-XY	0.490	12.45	0.120	3.05	0.120	3.05	0.250	6.35	OB
84693-XYH	0.975	24.77	0.380	9.65	0.380	9.65	0.215	5.46	OB
84819-XYH	0.730	18.54	0.110	2.79	0.170	4.32	0.450	11.43	OB
84950-XYH	1.250	31.75	0.120	3.05	0.350	8.89	0.780	19.81	OB
86816-XY	0.925	23.50	0.120	3.05	0.120	3.05	0.685	17.40	OB
86824-XY	0.760	19.30	0.120	3.05	0.250	6.35	0.390	9.91	OB
86826-XY	0.700	17.78	0.120	3.05	0.330	8.38	0.250	6.35	OB
86831-XY	0.525	13.34	0.100	2.54	0.225	5.72	0.200	5.08	OB
86869-XY	1.020	25.91	0.120	3.05	0.230	5.84	0.670	17.02	OB
87039-XY	1.240	31.50	0.120	3.05	0.120	3.05	1.000	25.40	OB
87053-XY	0.990	25.15	0.120	3.05	0.120	3.05	0.750	19.05	OB
87323-XY	1.375	34.93	0.219	5.56	0.406	10.31	0.750	19.05	OB

www.fciconnect.com			surface ISO 1302 ☒		tolerance std ISO 406 ISO 1101		projection 		INCH/MM ←→	
			TOLERANCES UNLESS OTHERWISE SPECIFIED						size A4	
Dr	T. BREWBAKER	1/31/95	ANGULAR		LINEAR		0.X		±0.3	
Eng	T. HANNA	1/31/95					0.XX		±0.15	
Chr	T. HANNA	1/31/95	0° ±2°				0.XXX		±0.05	
Appr	T. HANNA	1/31/95	Product family				BERGSTIK		Spec ref	
			title				BERGSTIK® II HDR. D/R			
							.100 CTR. R.R. TRACK			
			catalog no				dwg no			
							78563			
							Rev.			
							CX			
							CUSTOMER			
							sheet 4 of 7			

1

2

3

PDS: Rev :CX

STATUS:Released

Printed: Oct 29, 2013

1

2

3

4

A

B

C

D

A

B

C

D

PRODUCT NUMBER	TOTAL PIN LGTH		TAIL LENGTH		MATING LENGTH		HEIGHT ABOVE BOARD		LF OPTION
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	DIM J	DIM J	
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	
87324-XXX	1.218	30.94	0.406	10.31	0.406	10.31	0.406	10.31	OB
87346-XXX	0.930	23.62	0.100	2.54	0.330	8.38	0.500	12.70	OB
87347-XXX	0.890	22.61	0.110	2.79	0.280	7.11	0.500	12.70	OB
87501-XXXH	1.230	31.24	0.330	8.38	0.100	2.54	0.800	20.32	OB
87511-XXXH	1.130	28.70	0.105	2.67	0.325	8.26	0.700	17.78	OB
87512-XXXH	1.030	26.16	0.120	3.05	0.410	10.41	0.500	12.70	OB
87571-XXXH	0.930	23.62	0.250	6.35	0.250	6.35	0.430	10.92	OB
87594-XXX	1.190	30.23	0.200	5.08	0.120	3.05	0.870	22.10	OB
87887-XXX	0.940	23.88	0.120	3.05	0.395	10.03	0.425	10.80	OB
87899-XXX	1.040	26.42	0.120	3.05	0.370	9.40	0.550	13.97	OB
89444-XXX	0.930	23.62	0.120	3.05	0.310	7.87	0.500	12.70	OB
89637-XXX	1.260	32.00	0.118	3.00	0.315	8.00	0.827	21.01	OB
89638-XXX	1.040	26.42	0.120	3.05	0.270	6.86	0.650	16.51	OB
90237-XXX	0.813	20.65	0.120	3.05	0.318	8.08	0.375	9.53	OB
90608-XXX	0.595	15.11	0.120	3.05	0.255	6.48	0.220	5.59	OB
90806-XXX	1.400	35.56	0.360	9.14	0.200	5.08	0.840	21.34	OB
91507-XXXH	0.610	15.49	0.120	3.05	0.240	6.10	0.250	6.35	OB
91508-XXXH	0.888	22.56	0.120	3.05	0.500	12.70	0.268	6.81	OB
91509-XXXH	1.260	32.00	0.120	3.05	0.500	12.70	0.640	16.26	OB
91510-XXXH	0.960	24.38	0.120	3.05	0.500	12.70	0.340	8.64	OB
91862-XXXH	0.767	19.48	0.120	3.05	0.297	7.54	0.350	8.89	OB
91863-XXXH	0.792	20.12	0.120	3.05	0.297	7.54	0.375	9.53	OB

LF
OPTION

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection A4		INCH/MM ←→	
TOLERANCES UNLESS OTHERWISE SPECIFIED			ANGULAR		LINEAR		size		Scale	
Dr	T. BREWBAKER	1/31/95					A4		1.000	
Eng	T. HANNA	1/31/95								
Chr	T. HANNA	1/31/95	0° ±2°		0.XXX ±0.05		ECN			
Appr	T. HANNA	1/31/95	Product family				BERGSTIK		Spec ref	
FCI			title				BERGSTIK® II HDR, D/R		dwg no	
							.100 CTR, R.R. TRACK		78563	
			catalog no				CUSTOMER		Rev. CX	
									sheet 5 of 7	

1

2

3

4

1

2

3

4

A

B

C

D

A

B

C

D

PRODUCT NUMBER	TOTAL PIN LGTH		TAIL LENGTH		MATING LENGTH		HEIGHT ABOVE BOARD		LF OPTION
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	DIM J	DIM J	
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	
92002-XYHH	0.980	24.89	0.120	3.05	0.410	10.41	0.450	11.43	OB
92012-XYHH	0.940	23.88	0.090	2.29	0.350	8.89	0.500	12.70	OB
92013-XYHH	1.450	36.83	0.120	3.05	0.330	8.38	1.000	25.40	OB
92094-XYHH	1.030	26.16	0.180	4.57	0.180	4.57	0.670	17.02	OB
92628-XYHH	1.160	29.46	0.120	3.05	0.230	5.84	0.810	20.57	OB
92900-XYHH	0.470	11.94	0.110	2.79	0.110	2.79	0.250	6.35	OB
93223-XYHH	0.635	16.13	0.090	2.29	0.230	5.84	0.315	8.00	OB
94046-XYHH	0.620	15.75	0.120	3.05	0.250	6.35	0.250	6.35	OB
94082-XYHH	0.838	21.29	0.120	3.05	0.318	8.08	0.400	10.16	OB
94083-XYHH	1.398	35.51	0.120	3.05	0.318	8.08	0.960	24.38	OB
94084-XYHH	0.775	19.69	0.130	3.30	0.265	6.73	0.380	9.65	OB
94085-XYHH	0.825	20.96	0.130	3.30	0.265	6.73	0.430	10.92	OB
94550-XYHH	1.110	28.19	0.125	3.18	0.300	7.62	0.685	17.40	OB
94551-XYHH	1.120	28.45	0.415	10.54	0.415	10.54	0.290	7.37	OB
94552-XYHH	1.230	31.24	0.110	2.79	0.205	5.21	0.915	23.24	OB
94553-XYHH	1.230	31.24	0.120	3.05	0.310	7.87	0.800	20.32	OB
94554-XYHH	1.250	31.75	0.120	3.05	0.330	8.38	0.800	20.32	OB
94555-XYHH	1.270	32.26	0.385	9.78	0.385	9.78	0.500	12.70	OB
94605-XYHH	0.830	21.08	0.110	2.79	0.270	6.86	0.450	11.43	OB
94620-XYHH	1.002	25.45	0.120	3.05	0.382	9.70	0.500	12.70	OB
94621-XYHH	0.590	14.99	0.100	2.54	0.260	6.60	0.230	5.84	OB
94632-XYHH	1.040	26.42	0.110	2.79	0.305	7.75	0.625	15.88	OB
94672-XYHH	0.750	19.05	0.120	3.05	0.335	8.51	0.295	7.49	OB
95036-XYHH	1.304	33.12	0.290	7.37	0.290	7.37	0.724	18.39	OB
95063-XYHH	0.902	22.91	0.135	3.43	0.330	8.38	0.437	11.10	OB
95064-XYHH	0.630	16.00	0.220	5.59	0.120	3.05	0.290	7.37	OB
95088-XYHH	1.100	27.94	0.300	7.62	0.300	7.62	0.500	12.70	OB



Copyright FCI.

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection 	INCH/MM ←→
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	T. BREWBAKER	1/31/95	ANGULAR	LINEAR	0.X	±0.3
Eng	T. HANNA	1/31/95			0.XX	±0.15
Chr	T. HANNA	1/31/95			0.XXX	±0.05
Appr	T. HANNA	1/31/95	Product family		BERGSTIK	ECN
			title		BERGSTIK® II HDR. D/R	
			catalog no		.100 CTR. R.R. TRACK	
			dwg no		78563	
			CUSTOMER		sheet 6 of 7	

1

2

3

PDS: Rev :CX

STATUS:Released

Printed: Oct 29, 2013

1

2

3

4

A

B

C

D

A

B

C

D

PRODUCT NUMBER	TOTAL PIN LGTH		TAIL LENGTH		MATING LENGTH		HEIGHT ABOVE BOARD		LF OPTION
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	DIM J	DIM J	
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	
95116-XXYH	1.430	36.32	0.110	2.79	0.445	11.30	0.875	22.23	— OB
95124-XXYH	0.838	21.29	0.112	2.84	0.289	7.34	0.437	11.10	— OB
95129-XXYH	1.330	33.78	0.060	1.52	0.350	8.89	0.920	23.37	— OB
95616-XXYH	1.253	31.83	0.170	4.32	0.343	8.71	0.740	18.80	— OB
95656-XXYH	0.910	23.11	0.230	5.84	0.230	5.84	0.450	11.43	— OB
95657-XXYH	0.980	24.89	0.300	7.62	0.230	5.84	0.450	11.43	— OB
95685-XXYH	0.895	22.73	0.340	8.64	0.340	8.64	0.215	5.46	— OB
95686-XXYH	0.900	22.86	0.350	8.89	0.350	8.89	0.200	5.08	— OB
95711-XXYH	1.030	26.16	0.180	4.57	0.100	2.54	0.750	19.05	— OB
95731-XXYH	1.335	33.91	0.110	2.79	0.395	10.03	0.830	21.08	— OB
95762-XXYH	1.050	26.67	0.150	3.81	0.230	5.84	0.670	17.02	— OB
95787-XXYH	0.930	23.62	0.100	2.54	0.225	5.72	0.605	15.37	— OB
95788-XXYH	1.130	28.70	0.155	3.94	0.175	4.45	0.800	20.32	— OB
98048-XXYH	0.609	15.47	0.120	3.05	0.230	5.84	0.259	6.58	— OB
98049-XXYH	0.930	23.62	0.090	2.29	0.210	5.33	0.630	16.00	— OB
98070-XXYH	1.086	27.58	0.125	3.18	0.232	5.89	0.728	18.49	— OB
98141-XXYH	0.530	13.46	0.120	3.05	0.120	3.05	0.290	7.37	— OB
98216-XXYH	0.850	21.59	0.120	3.05	0.120	3.05	0.610	15.49	— OB
98836-XXYH	0.830	21.08	0.150	3.81	0.220	5.59	0.460	11.68	— OB
10007210-XXYH	1.130	28.70	0.220	5.59	0.460	11.68	0.450	11.43	— OB
10017135-XXYH	1.330	33.78	0.285	7.24	0.595	15.11	0.450	11.43	— OB
10017288-XXYH	1.331	33.81	0.160	4.06	0.210	5.33	0.961	24.41	— OB
10033859-XXYH	1.130	28.70	0.190	4.83	0.490	12.45	0.450	11.43	— OB
10037932-XXYH	1.230	31.24	0.190	4.83	0.590	14.99	0.450	11.43	— OB
10070373-XXYH	1.338	34.00	0.125	3.20	0.275	7.00	0.937	23.80	— OB
10117016-XXYH	0.695	17.66	0.240	6.10	0.240	6.10	0.215	5.46	NOTE 1,7
10117057-XXYH	0.805	20.45	0.120	3.05	0.217	5.50	0.469	11.90	— OB

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection ⊕		INCH/MM ←→	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	T. BREWBAKER	1/31/95	ANGULAR	LINEAR	0.X	±0.3	size A4	Scale 1.000		
Eng	T. HANNA	1/31/95			0.XX	±0.15				
Chr	T. HANNA	1/31/95			0.XXX	±0.05				
Appr	T. HANNA	1/31/95	Product family		BERGSTIK		Spec ref			
FCI			title BERGSTIK® II HDR, D/R .100 CTR, R.R. TRACK				dwg no 78563		Rev. CX	
			catalog no				CUSTOMER		sheet 7 of 7	

1

2

3

4