







	1	2	3	4	5	6	7																																													
A	 NOTES: ELECTRICAL: 1. VOLTAGE RATING : 125 VAC 2. CURRENT RATING : 1.5 AMP. 3. CONTACT RESISTANCE : 100 MILLIOHMS MAX. 4. INSULATION RESISTANCE : 1000 MEGOHMS MIN. @ 500 VDC. 5. DIELECTRIC STRENGTH : 750 VAC 60Hz, 1MIN. 6. CATEGORY 5e CHARACTERISTIC: <table data-bbox="960 1456 1193 1921"><tr><th>Frequency MHz</th><th>Insertion Loss dB, MIN.</th><th>Return Loss dB, MAX.</th><th>Attenuation dB, MAX.</th></tr><tr><td>1.0</td><td>65.0</td><td>35.5</td><td>0.1</td></tr><tr><td>4.0</td><td>65.0</td><td>35.5</td><td>0.1</td></tr><tr><td>8.0</td><td>64.9</td><td>35.5</td><td>0.1</td></tr><tr><td>10.0</td><td>63.0</td><td>35.5</td><td>0.1</td></tr><tr><td>16.0</td><td>58.9</td><td>35.5</td><td>0.2</td></tr><tr><td>20.0</td><td>57.0</td><td>34.0</td><td>0.2</td></tr><tr><td>25.0</td><td>55.0</td><td>32.0</td><td>0.2</td></tr><tr><td>31.25</td><td>53.1</td><td>30.1</td><td>0.2</td></tr><tr><td>62.5</td><td>47.1</td><td>24.0</td><td>0.3</td></tr><tr><td>100.0</td><td>43.0</td><td>20.0</td><td>0.4</td></tr></table> MECHANICAL: 1. HOUSING MATERIAL : PC UL94V-0 2. INSERT MATERIAL : GLASS FILLED POLYESTER UL94V-0 BK. 3. PCB MATERIAL : FR-4 THICKNESS 1.6mm 4. CONTACT MATERIAL : PHOSPHOR BRONZE STAMP PIN t=0.35mm ENVIRONMENTAL: 1. STORAGE: -40°C TO +85°C. 2. OPERATION: 0°C TO 70°C. CONFORMING TO TIA/EIA 568B MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68, SUBPART F.							Frequency MHz	Insertion Loss dB, MIN.	Return Loss dB, MAX.	Attenuation dB, MAX.	1.0	65.0	35.5	0.1	4.0	65.0	35.5	0.1	8.0	64.9	35.5	0.1	10.0	63.0	35.5	0.1	16.0	58.9	35.5	0.2	20.0	57.0	34.0	0.2	25.0	55.0	32.0	0.2	31.25	53.1	30.1	0.2	62.5	47.1	24.0	0.3	100.0	43.0	20.0	0.4	
Frequency MHz	Insertion Loss dB, MIN.	Return Loss dB, MAX.	Attenuation dB, MAX.																																																	
1.0	65.0	35.5	0.1																																																	
4.0	65.0	35.5	0.1																																																	
8.0	64.9	35.5	0.1																																																	
10.0	63.0	35.5	0.1																																																	
16.0	58.9	35.5	0.2																																																	
20.0	57.0	34.0	0.2																																																	
25.0	55.0	32.0	0.2																																																	
31.25	53.1	30.1	0.2																																																	
62.5	47.1	24.0	0.3																																																	
100.0	43.0	20.0	0.4																																																	
B																																																				
C																																																				
D																																																				
E																																																				
F																																																				
G	RoHS compliant Unit: mm ① File No.: E345352 <table data-bbox="90 573 448 750"><tr><th>Scale</th><th>Free</th><th></th></tr><tr><td colspan="3">TOLERANCE</td></tr><tr><td>.X</td><td>±0.20</td><td></td></tr><tr><td>.XX</td><td>±0.15</td><td></td></tr><tr><td>.XXX</td><td>±0.10</td><td></td></tr><tr><td>DIM</td><td>TOL</td><td>① Add UL</td></tr><tr><td>Angle</td><td>±5°</td><td>② Drawn</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td></tr><tr><td>Angle</td><td>TOL</td><td>Modification</td></tr><tr><td>Angle</td><td>TOL</td><td>Date</td></tr><tr><td>Angle</td><td>TOL</td><td>Name</td></tr></table> <table data-bbox="90 1326 448 1662"><tr><th>Date</th><th>Name</th><th></th></tr><tr><td>02.07.2013</td><td>Winnie</td><td>Drawn</td></tr><tr><td>24.03.2017</td><td>Amy</td><td>Approved</td></tr></table> ASSMANN WSW-No. A-TA3534 Drawing-No. ASS 5822 CO rev01 Replace Sheet							Scale	Free		TOLERANCE			.X	±0.20		.XX	±0.15		.XXX	±0.10		DIM	TOL	① Add UL	Angle	±5°	② Drawn	Angle	TOL	Id.	Angle	TOL	Modification	Angle	TOL	Date	Angle	TOL	Name	Date	Name		02.07.2013	Winnie	Drawn	24.03.2017	Amy	Approved			
Scale	Free																																																			
TOLERANCE																																																				
.X	±0.20																																																			
.XX	±0.15																																																			
.XXX	±0.10																																																			
DIM	TOL	① Add UL																																																		
Angle	±5°	② Drawn																																																		
Angle	TOL	Id.																																																		
Angle	TOL	Modification																																																		
Angle	TOL	Date																																																		
Angle	TOL	Name																																																		
Date	Name																																																			
02.07.2013	Winnie	Drawn																																																		
24.03.2017	Amy	Approved																																																		
H	1 2 3 4 5 6 7																																																			

CON0131