

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS			
GP	00	P	LTR	DESCRIPTION	DATE
		P		REVISED PER ECO-08-007327	14OCT08

D

C

B

A



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
- 3 MATERIAL:
HOUSING - THERMOPLASTIC (BLACK)
TERMINALS: - HIGH STRENGTH COPPER ALLOY PLATED WITH .000030 MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE .000030 MIN TOTAL ON MATING SURFACE. .000050 MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
4. WIRE SIZE: 24 & 26 AWG SOLID & 24 AWG 7 STRANDS OF COPPER CONDUCTORS. MAX INSULATION DIAMETER OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
- 5 CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF TYCO ELECTRONICS.

D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER	05OCT05	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK W. MILLHIMES	05OCT05				
	0 PLC ± -	APVD W. MILLHIMES	05OCT05	NAME ASSEMBLY, PLUG, 24 POSITION, B-SLOT CHAMP-LOK W/ 4-40 HOLES			
	1 PLC ± -	PRODUCT SPEC	—				
	2 PLC ± -	APPLICATION SPEC	—				
	3 PLC ± -	—	—				
4 PLC ± -	ANGLES ± -	WEIGHT	—	SIZE A2	CAGE CODE 00779	DRAWING NO C=552283	RESTRICTED TO —
MATERIAL 	FINISH 	CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 1	REV P

552283

552283-1
PART
NUMBER