



## "UNIVERSAL" FOR T-1 & T-1 3/4



- Unique design separates leads and retains Tri-Lead and Bi-Lead components.
- Designed for PC board mounting of Tri-Lead and Bi-Lead T-1 and T-1 3/4 LEDs
- Provides height control, lead retention and stability.
- Also suitable for mounting lamps, resistors, transistors, diodes, capacitors, etc.

**MATERIAL:** Black PVC, UL Rated 94V-0






| FOR T-1 3/4 and T-1 |            |          |             |
|---------------------|------------|----------|-------------|
| CAT. NO.            | L LENGTH   | CAT. NO. | L LENGTH    |
| 8900                | .120 (3.0) | 8916     | .400 (10.2) |
| 8901                | .140 (3.6) | 8917     | .420 (10.7) |
| 8902                | .160 (4.1) | 8918     | .440 (11.2) |
| 8903                | .180 (4.6) | 8919     | .450 (11.4) |
| 8904                | .200 (5.1) | 8920     | .460 (11.7) |
| 8905                | .220 (5.6) | 8921     | .480 (12.2) |
| 8906                | .240 (6.1) | 8922     | .500 (12.7) |
| 8907                | .250 (6.4) | 8923     | .550 (14.0) |
| 8908                | .260 (6.6) | 8924     | .600 (15.2) |
| 8909                | .280 (7.1) | 8925     | .650 (16.5) |
| 8910                | .300 (7.6) | 8926     | .700 (17.8) |
| 8911                | .320 (8.1) | 8927     | .750 (19.1) |
| 8912                | .340 (8.6) | 8928     | .800 (20.3) |
| 8913                | .350 (8.9) | 8929     | .850 (21.6) |
| 8914                | .360 (9.1) | 8930     | .900 (22.9) |
| 8915                | .380 (9.7) | 8931     | .925 (23.5) |

## "SELF-ALIGNING" FOR BI-LEAD T-1 & T-1 3/4

### KEY FEATURES

- Positive self-alignment of leads on .100 (.25) centers.
- No special tools required

**MATERIAL:** Natural Nylon, UL Rated 94V-2



- This features an internally tapered barrier which guides the leads and eliminates crimping or shorting.
- The bottom bosses serve the dual purpose of heat dissipation and easy post soldering cleanup.



| T-1 3/4 | T-1  | L LENGTH   | A REF.     |
|---------|------|------------|------------|
| 8311    | 7351 | .120 (3.0) | .075 (1.9) |
| 8312    | 7352 | .140 (3.6) |            |
| 8313    | 7353 | .160 (4.1) |            |
| 8314    | 7354 | .180 (4.6) |            |
| 8315    | 7355 | .200 (5.1) |            |
| 8316    | 7356 | .220 (5.6) | .190 (4.8) |
| 8317    | 7357 | .240 (6.1) |            |
| 8318    | 7358 | .250 (6.4) |            |
| 8319    | 7359 | .260 (6.6) |            |
| 8320    | 7360 | .280 (7.1) |            |
| 8321    | 7361 | .300 (7.6) | .200 (5.1) |
| 8322    | 7362 | .320 (8.1) |            |
| 8323    | 7363 | .340 (8.6) |            |
| 8324    | 7364 | .350 (8.9) |            |
| 8325    | 7365 | .360 (9.1) |            |
| 8326    | 7366 | .380 (9.7) | .325 (8.3) |

| T-1 3/4 | T-1  | L LENGTH    | A REF.      |
|---------|------|-------------|-------------|
| 8327    | 7367 | .400 (10.2) | .325 (8.3)  |
| 8328    | 7368 | .420 (10.7) |             |
| 8329    | 7369 | .440 (11.2) |             |
| 8330    | 7370 | .450 (11.4) |             |
| 8331    | 7371 | .460 (11.7) |             |
| 8332    | 7372 | .480 (12.2) | .450 (11.4) |
| 8333    | 7373 | .500 (12.7) |             |
| 8334    | 7374 | .550 (14.0) |             |
| 8335    | 7375 | .600 (15.2) |             |
| 8336    | 7376 | .650 (16.5) |             |
| 8337    | 7377 | .700 (17.8) | .575 (14.6) |
| 8338    | 7378 | .750 (19.1) |             |
| 8339    | 7379 | .800 (20.3) |             |
| 8340    | 7380 | .850 (21.6) |             |
| 8341    | 7381 | .900 (22.9) |             |
| 8342    | 7382 | .925 (23.5) | .690 (17.5) |

## "SELF-RETAINING" FOR T-1

- Features internal retention "teeth" which secure LED leads onto spacers.
- This features an internally tapered barrier which guides the leads and eliminates crimping or shorting.
- The bottom bosses serve the dual purpose of heat dissipation and easy post soldering cleanup.

**MATERIAL:** Natural Nylon, UL Rated 94V-2



### KEY FEATURES

- Internal design eliminates crimping or shorting of leads
- Self alignment of leads on .100 (.25) centers.
- Spacer will stay gripped to LED leads during assembly
- No special tools required

| T-1  | L LENGTH   | A REF.     |
|------|------------|------------|
| 7030 | .120 (3.0) | .060 (1.5) |
| 7031 | .140 (3.6) |            |
| 7032 | .160 (4.1) |            |
| 7033 | .180 (4.6) |            |
| 7034 | .200 (5.1) |            |
| 7035 | .220 (5.6) | .185 (4.7) |
| 7036 | .240 (6.1) |            |
| 7037 | .250 (6.4) |            |
| 7038 | .260 (6.6) |            |
| 7039 | .280 (7.1) |            |
| 7040 | .300 (7.6) | .310 (7.9) |
| 7041 | .320 (8.1) |            |
| 7042 | .340 (8.6) |            |
| 7043 | .350 (8.9) |            |
| 7044 | .360 (9.1) |            |
| 7045 | .380 (9.7) | .310 (7.9) |

| T-1  | L LENGTH    | A REF.      |
|------|-------------|-------------|
| 7046 | .400 (10.2) | .310 (7.9)  |
| 7047 | .420 (10.7) |             |
| 7048 | .440 (11.2) |             |
| 7049 | .450 (11.4) |             |
| 7050 | .460 (11.7) |             |
| 7051 | .480 (12.2) | .435 (11.0) |
| 7052 | .500 (12.7) |             |
| 7053 | .550 (14.0) |             |
| 7054 | .600 (15.2) |             |
| 7055 | .650 (16.5) |             |
| 7056 | .700 (17.8) | .650 (14.2) |
| 7057 | .750 (19.1) |             |
| 7058 | .800 (20.3) |             |
| 7059 | .850 (21.6) |             |
| 7060 | .900 (22.9) |             |
| 7061 | .925 (23.5) | .690 (17.5) |