


REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1902	A	RELEASED	EO	05/08/06	TL	06/15/06	HO	06/15/06



RoHS  
Compliant



9	INSULATION	POM	1	NONE
8	BODY	BRASS	1	NICKEL 100 $\mu$ " MIN.
7	CENTER CONTACT	BRASS	1	NICKEL 100 $\mu$ " MIN.
6	WASHER	BRASS	1	NICKEL 100 $\mu$ " MIN.
5	SPRING WSHR	SK-5	1	NICKEL 100 $\mu$ " MIN.
4	WASHER	BRASS	1	NICKEL 100 $\mu$ " MIN.
3	GASKET	RUBBER	1	NONE
2	INSULATION	POM	1	NONE
1	SHELL	BRASS	1	NICKEL 100 $\mu$ " MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

SPECIFICATIONS:

- 1- BODIES: BRASS PER JIS-C3604
- 2- CENTER CONTACT: BRASS PER JIS-C3604
- 3- CONNECTOR INTERFACE PER MIL-STD-348A
- 4- PART TO BE CLEAN AND FREE OF BURRS

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED  
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE  
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE  
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE  
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT  
FOR THE INTENDED USE AND ASSUME ALL RISK AND  
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:  
.X=±0.2  
.XX=±0.1  
.XXX=±0.05  
ANGLE=±5°

DRAWN BY:		DATE:		DRAWING TITLE:			
EKLAS ODISH		05/08/06		Coaxial Adapter, BNC Male To UHF Female, 50 Ohms			
CHECKED BY:		DATE:		SIZE		DWG. NO.	
THOMAS LEE		06/15/06		A		SPC20107	
APPROVED BY:		DATE:		ELECTRONIC FILE		REV	
HISHAM ODISH		06/15/06		82K9787.DWG		A	
SCALE: NTS				U.O.M.: mm [Inches]		SHEET: 1 OF 1	