

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

LOC

DIST

REVISIONS

© COPYRIGHT 20

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

FT

0

P

LTR

DESCRIPTION

DATE

DWN

APVD



C2

REVISED PER ECO-12-007964



03MAY2012

KH

MS



282815-3 AS SHOWN




1.00±0.02

2.54 REF

5.08±0.05

RECOMMENDED PC BOARD LAYOUT



1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.

2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.

3 END-TO-END STACKABLE WITHOUT LOSS OF
CENTERLINE SPACING.

4 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC.FILE N° E60677.

5 IMQ CERTIFICATE WITH SURVEILLANCE IN
CONFORMITY WITH IEC 998-1/998-2-1.

6 NOT CUMULATIVE TOLERANCE.

127.00	25	2-282815-5
121.92	24	2-282815-4
116.84	23	2-282815-3
111.76	22	2-282815-2
106.68	21	2-282815-1
101.60	20	2-282815-0
96.52	19	1-282815-9
91.44	18	1-282815-8
86.36	17	1-282815-7
81.28	16	1-282815-6
76.20	15	1-282815-5
71.12	14	1-282815-4
66.04	13	1-282815-3
60.96	12	1-282815-2
55.88	11	1-282815-1
50.80	10	1-282815-0
45.72	9	282815-9
40.64	8	282815-8
35.56	7	282815-7
30.48	6	282815-6
25.40	5	282815-5
20.32	4	282815-4
15.24	3	282815-3
10.16	2	282815-2

DIM. A N° OF POS. PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 25JUL2001

CHK E. ZANOLINI

D. BIEVENOUR

APVD 25JUL2001

D. BIEVENOUR

PRODUCT SPEC

108-20166

APPLICATION SPEC


114-20079

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±.
1 PLC ±.2
2 PLC ±.25
3 PLC ±.
4 PLC ±.
ANGLES ±2

MATERIAL



FINISH



TE Connectivity

NAME
TERMINAL BLOCK HEADER ASSEMBLY
90 DEGREE OPEN ENDS, STACKING
5.08mm PITCH

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779C-282815

SCALE 3:1 SHEET 1 OF 1 REV C2