





PART NO.
20021111



SQ 0.41 TYP.
Ø0.3 A B C



RECOMMENDED PCB LAYOUT

SCALE 5.000

- NOTES:
- 1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94-V0 BLACK.
TERMINAL: COPPER ALLOY
 - 2.THE HOUSING WILL WITHSTAND EXPOSURE TO 260~C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER OR VAPOR PHASE REFLOW OVEN.
 - 3.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - 4.PRODUCT SPEC: GS-12-629
 - 5.PACKAGE SPEC: GS-14-1420

mat'l. code				surface	tolerance	projection	product family			
				ISO 1302 ✓	ISO 406 ISO 1101	mm	MINITEK127®			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title			
E	ELX-N-23548	TIM	03/21/16	angles	.0±.30		UNSHROUDED HDR VT TH			
F	ELX-N-25883	TONY	01/11/17	linear	.00±.20					
G	ELX-N-27768	TONY	08/18/17	0°±2'	.000±.10	scale 1:1				
				dr	ZK HU	09/28/12	dwg no		sheet 1 of 2	size
				enr	ZK HU	09/28/12	20021111		A3	
				chr	BIAN RICK	09/28/12				
				appd	BIAN RICK	09/28/12	type		Product Customer Drawing	
sheet index	revision sheet	G	G							
		1	2							

PART NO.	POS.	DIM"X"	DIM"Y"
20021111-XXX92XXLF	2 X 46	58.42	57.15
20021111-XXX94XXLF	2 X 47	59.69	58.42
20021111-XXX96XXLF	2 X 48	60.96	59.69
20021111-XXX98XXLF	2 X 49	62.23	60.96
20021111-XXXA0XXLF	2 X 50	63.50	62.23

20021111 - X X X XX X X LF

—LEAD FREE

—PLATING OPTIONAL

1: GOLD FLASH AT CONTACT, 1.27 μ m MIN. MATTE TIN AT TAIL

2: GOLD FLASH AT CONTACT, GOLD FLASH AT TAIL

4: 0.25um Au MIN. AT CONTACT, 1.27um MIN.MATTE TIN AT TAIL

5: 0.25um Au MIN. AT CONTACT, GOLD FLASH AT TAIL

6: 0.38 μ m GXT MIN. AT CONTACT, 1.27 μ m MIN. MATTE TI

7: 0.38 μ m GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

8: 0.76 μ m GXT MIN. AT CONTACT. 1.27 μ m MIN. MATTE TI

9: 0.76um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

PACKING STYLE

—PACKING STYLE
T. TUBE

T: TUBE
O: TARE

Q: TAPE & REEL WITHOUT CAP
PIN NO. SEE TABLE

—PIN NO. SEE TABLE

—MATING LENGTH(DIM'A')

0: 3.05MM

— TAIL LENGTH(DIM"B")

Q: 2.30MM (FOR 1.6MM PCB)

1: 1.60MM (FDR 1.0MM PCB)

2: 2.70MM (FDR 2.0MM PCB)

RESERVE CODE

—RESERVE COD
0: STANDARD[illegible]