



REVISIONS			
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE	

業務部

STAKE IN 4 PLACES
EQUALLY SPACED 90° APART
(打四點 間隔 90°)
(SEE REMARK 1,2)



- REMARK:1. NO.2 MUST WITHSTAND A 6 lbs. MIN. PUSHOUT FORCE FROM NO.1 AFTER STAKING OPERATION
2. REMARK1 IS MAINTAINED BY STAMPING THE FOUR POINTS SHOWN ON THE DRAWING WITHOUT PUNCTURING NO.1
- (1. 打四點後零件 2 由零件 1 推出至少必須承受 6 磅推力)
- (2. 打四點後除需符合備註 1 要求外 且不可擊穿零件 1)

NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER QQ-B-626
2. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
3. BERYLLIUM COPPER PER QQ-C-530
4. GOLD PL. 50 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
5. TEFLON MIL-P-19468

出圖
2001.3.15
設計部

S. TEFLON MIL-P-19468					DIMENSIONS ARE IN MILLIMETERS				PART NO.		Amphenol – Kai Jack	
					UNLESS OTHERWISE SPECIFIED TOLERANCES						TAINAN TAIWAN	
					0.5-6 = ±0.2				APPROVED		TITLE	
					6-30 = ±0.4				DATE		SMA END LAUNCH RECEPT. JACK	
					30-120 = ±0.6				CHECKED		DRAWING NO.	
					120-315 = ±1				DATE		KJ-SMA6251A1-019-3GT50G-50	
					315-1000 = ±1.6				DRAWN		FILE NO.	
					1000-2000 = ±2.4				DATE		F:\DWG\SMA\6251A1\019\50\3GT50G-ES0	
3	CONTACT PIN	NOTE 3	NOTE 4	1	SMA87091603-3	SCALE	4/1	ISSUE	A			
2	INSULATOR	NOTE 5	NATURAL	1	SMA87091603-2T-50-B							
1	BODY	NOTE 1	NOTE 2	1	SMA87091603-1							