TOSHIBA PHOTOCOUPLER GaAs IRED & PHOTO-MOS FET

TLP206G

PBX

MODEM · FAX CARD

MEASUREMENT INSTRUMENT

Unit in mm



JEDEC	—
EIAJ	—
TOSHIBA	

Weight : 0.2 g

The TOSHIBA TLP206G consists of gallium arsenide infrared emitting diode optically coupled to a photo-MOS FET in a 8 pin SOP.
The TLP206G is a 2-Form-A switch which is suitable for replacement of mechanical relays in many applications.

- SOP 8 pin (2.54SOP8) : 2-Form-A
- Peak Off-State Voltage : 350 V (min)
- Trigger LED Current : 3 mA (max)
- On-State Current : 120 mA (max)
- On-State Resistance : 35 Ω (max)
- Isolation Voltage : 1500 V_{rms} (min)
- UL Recognized : UL1577, File No. E67349
- BSI Approved : BS EN60065 : 1994, Certificate No. 8273
  BS EN60950 : 1992, Certificate No. 8274
- SEMKO Approved : SS EN60065
  SS EN60950
- Option (V4) type
  TUV Approved : DIN VDE0884 / 06.92,
  Certificate No. R9850580

SCHEMATIC



PIN CONFIGURATION (TOP VIEW)



1, 3 : ANODE
2, 4 : CATHODE
5 : DRAIN D1
6 : DRAIN D2
7 : DRAIN D3
8 : DRAIN D4

000707EBC2

MAXIMUM RATINGS (Ta = 25°C)

	CHARACTERISTIC		SYMBOL	RATING	UNIT
LED	Forward Current		I_F	50	mA
	Forward Current Derating (Ta ≧ 25°C)		ΔI_F / °C	−0.5	mA / °C
	Pulse Forward Current (100 μs pulse, 100 pps)		I_{FP}	1	A
	Reverse Voltage		V_R	5	V
	Junction Temperature		T_j	125	°C
DETECTOR	Off-State Output Terminal Voltage		V_{OFF}	350	V
	On-State Current	Both Channel (Note 1)	I_{ON}	100	mA
		One Channel		120	
	On-State RMS Current Derating (Ta ≧ 25°C)	Both Channel (Note 1)	ΔI_{ON} / °C	−1.0	mA / °C
		One Channel		−1.2	
	Junction Temperature		T_j	125	°C
Storage Temperature Range			T_{stg}	−55~125	°C
Operating Temperature Range			T_{opr}	−40~85	°C
Lead Soldering Temperature (10 s)			T_{sol}	260	°C
Isolation Voltage (AC, 1 min., R.H. ≦ 60%) (Note 2)			BV_S	1500	V_{rms}

(Note 1) : Two channels operating simultaneously.
(Note 2) : Device considered a two-terminal device : pins 1, 2, 3 and 4 shorted together and pins 5, 6, 7 and 8 shorted together.

RECOMMENDED OPERATING CONDITIONS

CHARACTERISTIC	SYMBOL	MIN.	TYP.	MAX.	UNIT
Supply Voltage	V_{DD}	—	—	280	V
Forward Current	I_F	5	7.5	25	mA
On-State Current	I_{ON}	—	—	100	mA
Operating Temperature	T_{opr}	−20	—	65	°C

INDIVIDUAL ELECTRICAL CHARACTERISTICS (Ta = 25°C)

	CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
LED	Forward Voltage	V_F	I_F = 10 mA	1.0	1.15	1.3	V
	Reverse Current	I_R	V_R = 5 V	—	—	10	μA
	Capacitance	C_T	V = 0, f = 1 MHz	—	30	—	pF
DETECTOR	Off-State Current	I_{OFF}	V_{OFF} = 350 V	—	—	1	μA
	Capacitance	C_{OFF}	V = 0, f = 1 MHz	—	40	—	pF

COUPLED ELECTRICAL CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Trigger LED Current	I_{FT}	I_{ON} = 120 mA	—	1	3	mA
On-State Resistance	R_{ON}	I_{ON} = 120 mA, I_F = 5 mA	—	22	35	Ω

ISOLATION CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Capacitance Input to Output	C_S	V_S = 0, f = 1 MHz	—	0.8	—	pF
Isolation Resistance	R_S	V_S = 500 V, R.H. ≦ 60%	5×10^{10}	10^{14}	—	Ω
Isolation Voltage	BV_S	AC, 1 minute	1500	—	—	V_{rms}
		AC, 1 second, in oil	—	3000	—	V_{rms}
		DC, 1 minute, in oil	—	3000	—	Vdc

SWITCHING CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Turn-on Time	t_{ON}	R_L = 200 Ω (Note 3)	—	0.3	1	ms
Turn-off Time	t_{OFF}	V_{DD} = 20 V, I_F = 5 mA	—	0.1	1	ms

(Note 3) : Switching Time Test Circuit





I_F – Ta



I_{ON} – Ta



I_{FP} – D_R



I_F – V_F



$\Delta V_F / \Delta Ta$ – I_F



I_{FP} – V_{FP}



I_{FT} – Ta



I_{ON} – V_{ON}



R_{ON} – Ta



I_{OFF} – Ta



t_{ON} – Ta



t_{OFF} – Ta