





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		F	EC 0G3C 0745 04	10JAN05	BSV JRO
			F1	ECO-09-020932	26AUG09	KK AEG



RECOMMENDED HOLE LAYOUT

- 1
- PART NUMBER AND DATE CODE MARKED IN APPROXIMATE LOCATION SHOWN
- 2
- CONTACT: DUPLEX PLATED: .000010 GOLD ON CONTACT AREA, .000150-.000300 BRIGHT TIN-LEAD ON SOLDER LEADS, ALL OVER .000050 MINIMUM NICKEL.
3.
- TOLERANCE IS NON-CUMULATIVE.
- 4
- POINT OF MEASUREMENT FOR PLATING THICKNESS (MEASURED INSIDE CONTACT BEAMS)
- 5
- POINT OF CONTACT MEASUREMENT.
6.
- MATERIAL: HOUSING: GLASS FILLED POLYESTER-COLOR: BLACK
CONTACT: PHOSPHOR BRONZE
- 7
- CONTACT: DUPLEX PLATED: .000010 GOLD ON CONTACT AREA, .000150-.000300 MATTE TIN ON SOLDER LEADS, ALL OVER .000050 MINIMUM NICKEL.
- 8
- ROHS 2002/95/EC COMPLIANT
- 9
- TYCO LOGO AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION.
- 10
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	52	1,2,29&30	1,2,29&30		3.000	2.900	60	5-102766-4
OBSOLETE	44	1,2,25&26	1,2,25&26		2.600	2.500	52	5-102766-3
	30	1,2,18&19	1,2,18&19		1.900	1.800	38	5-102766-2
	40	1,2,23&24	1,2,23&24		2.400	2.300	48	5-102766-1
	52	1,2,29&30	1,2,29&30		3.000	2.900	60	102766-4
OBSOLETE	44	1,2,25&26	1,2,25&26		2.600	2.500	52	102766-3
	30	1,2,18&19	1,2,18&19		1.900	1.800	38	102766-2
 SUPERCEDED	40	1,2,23&24	1,2,23&24		2.400	2.300	48	102766-1
	NO ACTIVE POS	ROW Y	ROW Z	FINISH	A	B	NO OF POSN	PART NO
		CONTACTS OMITTED						

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 14-5-81
CHK 15-5-81
APVD 20-5-81

PRODUCT SPEC
APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH

CONTACTS: SEE TABLE

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME

CONNECTOR ASSY., MOD II/IV
DOUBLE ROW, .100 X .100 C/L, VERTICAL MOUNTED

SIZE A2
CAGE CODE 00779
DRAWING NO C=102766

RESTRICTED TO -

SCALE 4:1

SHEET 1 OF 1

REV F1