



NOTES:

2. CABLE ASSEMBLY TO BE 100% TESTED FOR HI POT, CONTINUITY, SHORTS AND OPEN.

115101-05-XX.XX		REVISIONS				
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR	
THIRD ANGLE PROJ. 	A	RELEASE TO MFG.	18-May-10	--	CL	



LENGTH TABLE	
PART NUMBER	LENGTH (IN.)
115101-05-06.00	06.00 $\pm$ 0.25
115101-05-12.00	12.00 $\pm$ 0.25
115101-05-24.00	24.00 $\pm$ 0.50
115101-05-36.00	36.00 $\pm$ 0.50

* ADDITIONAL LENGTHS CAN BE PROVIDED
BY CHANGING XX.XX TO DESIRED LENGTH IN INCHES
CONTACT CONNEX MARKETING FOR QUOTE

DESIGN REQUIREMENTS:

- | | |
|--|---|
| ☐ FREQUENCY: --- TO --- GHz | ☒ CONTINUITY |
| ☐ VSWR ----- : 1 MAX | ☒ HI-POT :1000 VRMS |
| ☐ INS. LOSS ----- dB MAX | ☐ OTHER |

009-954-341	A/R	3	HEAT SHRINK TUBE	BLACK
009-881-005	A/R	2	RG 179 CO-AXIAL CABLE	
112954	2	1	TRUE 75 OHM BNC CRIMP PLUG	
PART NUMBER	QTY	ITEM	DESCRIPTION	FINISH

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN CLEMENT	DATE 18-May-10	TITLE TRUE 75 OHM BNC CRIMP PLUG TO TRUE 75 OHM BNC CRIMP PLUG USING, RG 179 CABLE, VARIOUS LENGTHS			Amphenol Connex			
	REFERENCE	ENGINEER CLEMENT	DATE 18-May-10							
			APPROVED				DATE			
		CAD FILE	DWG SIZE B			DRAWING NO. 115101-05-XX.XX			REV A	