


ENERGIZER NO. X93



Industry Standard Dimensions in mm (inches)




Negative cover detail referenced on page 2

Chemical System:	Alkaline Zinc-Manganese Dioxide (Zn/MnO ₂) (No Added Mercury or Cadmium)
Designation:	ANSI-14A, IEC-LR14
Battery Voltage:	1.5 Volts
Internal Resistance:	324 Milliohms (Fresh)
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Average Capacity:	9,150 mAh (to 0.8 volts) (Rated capacity at 25 mA continuous drain)
Average Weight:	66.2 grams (2.3 oz.)
Volume:	26.9 cubic centimeters (1.6 cubic inch)
Cell:	One No. X3-335 (size 'C')
Jacket:	Plastic Label
Shelf Life:	7 years (80% of rated capacity)


TEMPERATURE EFFECTS

Typical Service to 0.8 Volts




CONSTANT RESISTANCE PERFORMANCE

Typical Service



CONSTANT CURRENT DISCHARGE

Typical Service







Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved

ENERGIZER NO. X93**Industry Standard Tests @ 20° C****Important Notice**

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved