


Title: Socket terminus Size 12

 Série
Termini

 Issue
Mar 10 2003

 Page
1/1

Dimensions : mm


GENERAL

- Type:** Termini #12 (Mil-T-29504)
Socket contact with ceramic ferrule and sleeve for UTE.C 93425 / HE 510 (EPX)
- Fibre:** Mutimode 100/140µm
- Cable:** Tight buffered single fiber optical cable.
Jacket maximum diameter : 1.5 mm
- Installation:** Bonding and polishing. See instructions 503 08 510 and F724 PC 04

CHARACTERISTICS (depending on fibre or cable construction)

- Optical:** 100/140 fibre size, $\lambda = 850$ nm
Typical insertion loss for a mated pair : 0.8dB, standard deviation = 0.2 db
(CEI 874 -1 / 4.4.7 method 6).
- Mechanical:** Mechanical endurance : 500 matings.
Cable retention : 27.8 N maxi.
Vibrations : 10-2000 Hz, 15 g.
Shocks : 50 g, 11 ms.
- Environmental:** Category : -55°C to +125°C.
High temperature resistance : 1000 h, 125°C.
Salt spray : 48 h.

CREATION					RADIALL®
N°:					101, rue P. Hoffmann
Nom: H.P.					93116 ROSNY/BOIS
Date: Jun 06 1989					FRANCE
Vérif.: A.M.	10/03/03	Added the Instructions 503 08 510	G.M.		Tel : (33) 0149353535
	Edition	Modification	Nom	Vérif.	Fax : (33) 0148546363

Ces renseignements sont donnés à titre indicatif. Dans le but constant d'améliorer nos produits, nous nous réservons le droit d'apporter toutes modifications jugées utiles