



DESCRIPTION: WIRE WRAP FILTERED D-SUB

	A	B	C
9	1.204	.984	.480
	30.60	25.00	12.20
15	1.535	1.312	.480
	39.00	33.30	12.20
25	2.078	1.850	.480
	52.80	47.00	12.20
37	2.724	2.500	.480
	69.20	63.50	12.20
50	2.622	2.405	.598
	66.60	61.10	15.20



477-XXX-242-XX1

SERIES _____
POSITIONS _____
009 _____
015 _____
025 _____
037 _____
050 _____
GENDER _____
1 = MALE
2 = FEMALE
TERMINATION _____
4 = WIRE WRAP
SHELL PLATING _____
2 = TIN
HARDWARE OPTIONS _____
00 = NO HARDWARE
PLATING OPTIONS _____
1 = GOLD FLASH

SPECIFICATIONS:

MATERIALS:

SHELL: STEEL, TIN PLATED
INSULATOR: UL 94V-0 RATED PBTP
GLASS-FIBER REINFORCED

ELECTRICALS:

INDIVIDUAL CAPACITOR VALUE = 1000 pF
OTHER VALUES AVAILABLE: CONSULT FACTORY
CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: <10 mOHMS
INSULTOR RESISTANCE: 1010 OHMS
VOLTAGE: 1 KV / AC
TEMPERATURE: -55°C TO +125°C

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: WAYNE ROBBINS		DATE: 9-03-98	
			CHECKED:		DATE:	
			SCALE: 1:1		SHEET 1 OF 1	
DWG NO. 477-XXX-242-001			REV 2			