



	1	2	3	4	5	6	7																																																																																															
A									A																																																																																													
B									B																																																																																													
C									C																																																																																													
D									D																																																																																													
E									E																																																																																													
F	Material: · SJT 3x14AWG(2.08MM²) VW-1 Shielded, 60° 300V,Without Filler · Jacket Color: Black · E- Green; L- Black; N- White Electrical Test : · 100% Open & Short Testing · Insulation Resistance : 100meg-ohm(Min.) · Voltage : 500V DC / 1 Min.								F																																																																																													
G	<table><tr><td>Scale</td><td>Free</td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Title</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>25.06.13</td><td>Wilson</td></tr><tr><td>X.</td><td>±X</td><td></td><td></td><td></td><td></td><td>Approved</td><td>25.06.13</td><td>Groll</td></tr><tr><td>X.X</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.X°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr></table> Unit: mm RoHS Compliant ASSMANN components 1940 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us <table><tr><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td>Replace</td><td>Sheet</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td>1/1</td></tr></table>								Scale	Free					Date	Name	Title	TOLERANCE						Drawn	25.06.13	Wilson	X.	±X					Approved	25.06.13	Groll	X.X	±X								X.XX	±X								DIM	TOL								X.°	±X°								X.X°	±X°								Angle	TOL								Id.	Modification	Date	Name	Replace	Sheet						1/1	G
Scale	Free					Date	Name	Title																																																																																														
TOLERANCE						Drawn	25.06.13	Wilson																																																																																														
X.	±X					Approved	25.06.13	Groll																																																																																														
X.X	±X																																																																																																					
X.XX	±X																																																																																																					
DIM	TOL																																																																																																					
X.°	±X°																																																																																																					
X.X°	±X°																																																																																																					
Angle	TOL																																																																																																					
Id.	Modification	Date	Name	Replace	Sheet																																																																																																	
					1/1																																																																																																	
H	Power cord - Plug ⇄ Open End SJT, 14AWG, 60°C, Shielded, 0.5 meter ASSMANN WSW-No. AK500/14-OE-5-0.5 Drawing-No. rev00								H																																																																																													
	1	2	3	4	5	6	7																																																																																															