






REV.	DATE	DESCRIPTION
A	05/29/03	UPDATE DRAWING FORMAT
B	08/13/07	REVISE PART ORIENTATION



PCB MOUNTING PATTERN



PANEL CUTOUT

NOTE:

1. REF: HUGHS 1016844-0001
2. BER. COPPER PLATING PER QQ-C-530

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex							
8					DRAWN	G.R.S.						08/13/07		
7					CHECKED			PART DESCRIPTION F SERIES R/A PCS RECEPTACLE						
6					ISSUED									
5	INSULATOR	DELRI	NATURAL		1	SHEET	1 OF 1	PART NO. 222128–10						
4	INSULATOR	POLY PRO	NATURAL		1									
3	CONTACT PIN	BER. COPPER	BRT. TIN		1			222128–10						
2	CONTACT PIN	BRASS	BRT. TIN		1									
1	BODY	BRASS	NICKEL	1	CAD FILE		DWG. NO.	222128–10.DWG	REV.	B	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY		C:/222/222128–10.DWG								