

FAST RECOVERY DIODES

Stud Version

Features

- High power FAST recovery diode series
- 1.5 to 2.0 μ s recovery time
- High voltage ratings up to 1600V
- High current capability
- Optimized turn on and turn off characteristics
- Low forward recovery
- Fast and soft reverse recovery
- Compression bonded encapsulation
- Stud version JEDEC DO-205AB (DO-9)
- Maximum junction temperature 125°C
- RoHS Compliant


250A

Typical Applications

- Snubber diode for GTO
- High voltage free-wheeling diode
- Fast recovery rectifier applications

Major Ratings and Characteristics

Parameters	SD253N/R	Units
$I_{F(AV)}$	250	A
@ T_C	85	°C
$I_{F(RMS)}$	392	A
I_{FSM} @ 50Hz	5350	A
@ 60Hz	5600	A
I^2t @ 50Hz	143	KA ² s
@ 60Hz	130	KA ² s
V_{RRM} range	400 to 1600	V
t_{rr} range	1.5 to 2.0	μ s
@ T_J	25	°C
T_J	- 40 to 125	°C



case style
DO-205AB (DO-9)

ELECTRICAL SPECIFICATIONS

Voltage Ratings


Type number	Voltage Code	V_{RRM} max. repetitive peak and off-state voltage V	V_{RSM} , maximum non-repetitive peak voltage V	I_{RRM} max. $T_J = 125^\circ\text{C}$ mA
SD253N/R..S15	04	400	500	35
	08	800	900	
	10	1000	1100	
SD253N/R..S20	12	1200	1300	
	14	1400	1500	
	16	1600	1700	

Forward Conduction

Parameter	SD253N/R	Units	Conditions
$I_{F(AV)}$ Max. average forward current @ Case temperature	250	A	180° conduction, half sine wave.
	85	°C	
$I_{F(RMS)}$ Max. RMS current	392	A	DC @ 74°C case temperature
I_{FSM} Max. peak, one-cycle non-repetitive forward current	5350	A	t = 10ms No voltage
	5600		t = 8.3ms reappplied
	4500		t = 10ms 100% V_{RRM}
	4710		t = 8.3ms reappplied
I^2t Maximum I^2t for fusing	143	KA^2s	t = 10ms No voltage
	130		t = 8.3ms reappplied
	101		t = 10ms 100% V_{RRM}
	92		t = 8.3ms reappplied
$I^2\sqrt{t}$ Maximum $I^2\sqrt{t}$ for fusing	1430	$\text{KA}^2\sqrt{\text{s}}$	t = 0.1 to 10ms, no voltage reappplied
$V_{F(TO)1}$ Low level of threshold voltage	0.87	V	$(16.7\% \times \pi \times I_{F(AV)} < I < \pi \times I_{F(AV)})$, $T_J = T_J \text{ max.}$
$V_{F(TO)2}$ High level of threshold voltage	1.17		$(I > \pi \times I_{F(AV)})$, $T_J = T_J \text{ max.}$
r_{f1} Low level of forward slope resistance	0.62	$\text{m}\Omega$	$(16.7\% \times \pi \times I_{F(AV)} < I < \pi \times I_{F(AV)})$, $T_J = T_J \text{ max.}$
r_{f2} High level of forward slope resistance	0.29		$(I > \pi \times I_{F(AV)})$, $T_J = T_J \text{ max.}$
V_{FM} Max. forward voltage	1.38	V	$I_{pk} = 785\text{A}$, $T_J = 25^\circ\text{C}$, $t_p = 400 \mu\text{s}$ square pulse

Recovery Characteristics

Code	$T_J = 25^\circ\text{C}$ typical t_{rr} @ 25% I_{RRM} (μs)	Test conditions			Max. values @ $T_J = 125^\circ\text{C}$		
		I_{pk} Square Pulse (A)	di/dt (A/ μs)	V_r (V)	t_{rr} @ 25% I_{RRM} (μs)	Q_{rr} (μC)	I_{rr} (A)
S15	1.5	750	25	-30	2.9	90	44
S20	2.0				3.2	107	46



Thermal and Mechanical Specification

Parameter	SD253N/R	Units	Conditions
T_J Max. operating temperature range	-40 to 125	°C	
T_{stg} Max. storage temperature range	-40 to 150		
R_{thJC} Max. thermal resistance, junction to case	0.115	K/W	DC operation
R_{thCS} Max. thermal resistance, case to heatsink	0.08		Mounting surface, smooth, flat and greased
T Mounting torque $\pm 10\%$	31	N m	Not lubricated threads
	24.5		Lubricated threads
wt Approximate weight	250	g	
Case style	DO-205AB (DO-9)		See Outline Table

ΔR_{thJC} Conduction

(The following table shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC)

Conduction angle	Sinusoidal conduction	Rectangular conduction	Units	Conditions
180°	0.010	0.008	K/W	$T_J = T_J \text{ max.}$
120°	0.013	0.014		
90°	0.017	0.019		
60°	0.025	0.027		
30°	0.044	0.044		

Ordering Information Table

Device Code								
SD	25	3	R	16	S20	P	B	V
①	②	③	④	⑤	⑥	⑦	⑧	⑨
1	- Diode							
2	- Essential part number							
3	- 3 = Fast recovery							
4	- N = Stud Normal Polarity (Cathode to Stud) R = Stud Reverse Polarity (Anode to Stud)							
5	- Voltage code: Code x 100 = V_{RRM} (see Voltage Ratings table)							
6	- t_{rr} code (see Recovery Characteristics table)							
7	- P = Stud base DO-205AB (DO-9) 3/4" 16UNF-2A M = Stud base DO-205AB (DO-9) M16 X 1.5							
8	- B = Flag top terminals (for Cathode/ Anode Leads) S = Isolated lead with silicone sleeve (Red = Reverse Polarity; Blue = Normal Polarity) None = Not isolated lead							
9	- V = Glass-metal seal							

Bulletin I2065 rev. B 10/06

GLASS-METAL SEAL

200 (7.87) ± 10 (0.39)

75 (2.95) MIN.

19 (0.75) MAX.

4 (0.16) MAX.

39 (1.53) MAX.

9.5 (0.37) MIN.

DIA. 8.5 (0.33) NOM.

DIA. 28.5 (1.08) MAX.

28.5 (1.12) MAX.

16 (0.63) MAX.

21 (0.82) MAX.

3/4-16UNF-2A*

SW 32

C.S. 35mm² (0.054 s.i.)

Conform to JEDEC DO-205AB (DO-9)

All dimensions in millimeters (inches)

* FOR METRIC DEVICE: M16 X 1.5

GLASS-METAL SEAL

21 (0.83)

14 (0.55)

DIA. 6.5 (0.26)

13 (0.51)

70 (2.75) MAX.

DIA. 28.5 (1.12) MAX.

28.5 (1.12) MAX.

16 (0.63) MAX.

21 (0.83) MAX.

62 (2.44)

3/4"-16UNF-2A*

DO-205AB (DO-9) Flag

All dimensions in millimeters (inches)

*FOR METRIC DEVICE: M16 X 1.5

32 (1.26)

3 (0.12)




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 3 - Forward Power Loss Characteristics




Fig. 4 - Forward Power Loss Characteristics




Fig. 5 - Maximum Non-repetitive Surge Current




Fig. 6 - Maximum Non-repetitive Surge Current




Fig. 7 - Forward Voltage Drop Characteristics



Fig. 8 - Thermal Impedance Z_{thJC} Characteristic

Fig. 9 - Recovery Time Characteristics




Fig. 10 - Recovery Charge Characteristics




Fig. 11 - Recovery Current Characteristics




Fig. 12 - Recovery Time Characteristics




Fig. 13 - Recovery Charge Characteristics




Fig. 14 - Recovery Current Characteristics




Fig. 15 - Maximum Total Energy Loss Per Pulse Characteristics




Fig. 16 - Maximum Total Energy Loss Per Pulse Characteristics

Data and specifications subject to change without notice.
This product has been designed and qualified for Industrial Level.
Qualification Standards can be found on IR's Web site.