

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1712248011

Status:

Active

Overview:

High-Speed Pluggable I/O Solutions

Description:

zSFP+ Stacked Ganged Assembly with Metal Spring Fingers, 2-by-8 with 4 Light Pipes, 320 Circuits

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

I/O Connectors

171224

Module-to-Board

Receptacle

High-Speed Pluggable I/O Solutions

zSFP Plus, zSFP+

N/A

884982824492

Physical

Circuits (Loaded)

Color - Resin

Durability (mating cycles max)

Flammability

Gender

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Ports

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

320

Black

100

94V-0

Female

Yes

High Performance Alloy (HPA)

Gold

Matte Tin

High Temperature Thermoplastic

190.032/g

2

Right Angle

Yes

Yes

2.36mm

Tray

No

0.80mm

0.80mm

0.762µm

0.762µm

Yes

Yes

16

No

-40° to +85°C

Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact


Shield Type

Shielded

0.5A

N/A

Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

171224 Series

Voltage - Maximum	30V AC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	

This document was generated on 07/27/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION