






LOC	DIST	REVISIONS				
AJ	16	P	LTR	DESCRIPTION	DATE	DWN
		BL1	REVISED	PER ECO-11-005030	11MAR11	RK

1. SEE IS 1770
2. BRASS PER QQ-B-626
3. NYLON PER ASTM-D-4066, NATURAL.
4. POLYMETHYLPENTENE GENERAL PURPOSE.
5. .000030 MINIMUM GOLD PER MIL-G-45204.
6. .000100 MINIMUM GOLD PER MIL-G-45204.



RECOMMENDED STRIP LENGTH

OBSOLETE	5	6	.042±.003	1-201146-0
	6	6	.042±.003	201146-9
SUPERSEDED BY 201146-2	5	5	.023±.003	201146-6
	5	5	.042±.003	201146-4
	5	5	.023±.003	201146-2
SUPERSEDED BY 201146-4	5	5	.042±.003	201146-1

		CONTACT PLATING		SHELL PLATING		"Y" DIM		PART NUMBER					
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN B. WERNER 8-9-94		 TE Connectivity							
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		CHK J. McLEOD 8-9-94						NAME			
		APVD J. McLEOD 8-9-94		PRODUCT SPEC		SOCKET. MINIATURE SERIES							
		0 PLC ± —		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		1 PLC ± —		—		A1		00779		C=201146		—	
		2 PLC ± 0.20 [.008]		WEIGHT		—		SCALE		8:1		SHEET	
		3 PLC ± —		—		—		—		—		1 OF	
		4 PLC ± —		CUSTOMER DRAWING		—		REV		BL1		—	
		5 ANGLES ± —		—		—		—		—		—	
MATERIAL		FINISH		—		—		—		—		—	
				—		—		—		—		—	